


PART No.	WIRE GA. / COLOR	"A"
0FNY0001ZXJ	#14 BLACK	203.2±5 (8.0)



- NOTES:
1. MAX FUSE RATING: 20A, 32VDC.
 2. MAX. OPERATING TEMPERATURE: 80°C.
 3. WIRE: COPPER STRANDED, UL 1015.
 4. CONTACTS: C2680 ALLOY.
 5. CRIMP: MUST MEET USCAR 21 STANDARD.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

CPK DENOTES CRITICAL CHARACTERISTICS.
 CPK DENOTES CPK DIMENSIONS--MINIMUM CPK VALUE
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT IS TO BE DETERMINED BY THE INSPECTOR OR INSPECTION INSTRUCTIONS.
 CPK DENOTES CP DIMENSIONS--MINIMUM CP VALUE DENOTES CP VALUE WITHIN THE DIMENSIONAL LIMITATIONS OF PROCESS PERFORMANCE AND INITIALLY LOCATED TO A DIMENSION FOR MAXIMUM TOOL LIFE.

COPIES TO		MATERIAL SPEC		FINISH	
1	9	DRW	DWM	DATE	09/05/08
2	10	CHK		DATE	
3	12			DATE	
4	13			DATE	
5	14	APPD		DATE	
6	15			DATE	
7	16			DATE	
8	17			DATE	
				TOLERANCE UNLESS OTHERWISE SPECIFIED	
				TWO PLACE DEC ±.01	
				THREE PLACE DEC ±.005	
				ANGULAR ±1°	
				LBS/IN	

LTR	REVISION	CHK	APD
A	000490ER-RELEASED 9/05/08		

TITLE
 FUSEHOLDER, INLINE (WITH FUSE)

REVISION	DRWG. NO.	OUTLINE
A	0FNY0001ZXJ	



UNCONTROLLED DOCUMENT