



NOTES:

- MATERIAL:
BASE: UL94V-0 GLASS FILLED NYLON
STUDS: M5
- TORQUE RATING: 5±1 Nm
- FUSE RATING: 30-200A
- WIRE SIZE: 14-4 AWG (2.5mm²-20mm²)
- TEMPERATURE RATING: -40°C TO 125°C

PACKAGING NOTES:

- PARTS ARE PACKED 50 PC PER BAG, 10 BAGS PER BOX.

METRIC
ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

◎ DENOTES CRITICAL CHARACTERISTICS.
CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				

LTR	DATE	REVISION	CHK	APD	COPIES TO	MATL SPEC
A	10/Aug/16	516244GCC-RELEASE FYUE			1 9 18 2 10 19 3 12 20 4 13 21 5 14 23 6 15 33 7 16 43 8 17 53	FINISH
						DRW FYUE DATE 10/Aug/16 SCALE 1:1 CHK DATE SUPER DR APPD DATE FINISH GOOD WT GRAMS/PIECE
						TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK) DIMENSION UP TO 0.5 -3 UP TO 3 -6 UP TO 6 -30 UP TO 30 -120 UP TO 120 -400 TOLERANCE ±0.1 ±0.1 ±0.1 ±0.2 ±0.3 ±0.5
						3RD ANGLE PROJECTION
						TITLE BASE FOR MIDI INLINE HOLDER, W/M5 BOLTS
						REVISION DRWG. NO. OUTLINE
						A OL-498921-3

