



# METRIC COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [ ] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
◎		DENOTES CRITICAL CHARACTERISTICS.		
CPK		DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
ⓈT		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
CP		DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		

COPIES TO		MATL SPEC	
1	9	2.0mm MS PLATE	
2	10	FINISH ZINC CHROMATE PLATED (t = 3-8 microns)	
3	12	DRW	DATE 21/Jun/16
4	13	FYUE	SCALE 1:1
5	14	CHK	DATE
6	15	APPD	DATE
7	16	FINISH	SUPER DR
8	17	WT	FINISH GOOD
9	18		WT
10	19	TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)	
11	20	DIMENSION	UP TO OVER UP TO OVER UP TO OVER UP TO OVER
12	21	0.5 - 3	3 - 6 6 - 30 30 - 120 120 - 400
13	22	TOLERANCE	+0.1 ±0.1 ±0.2 ±0.3 ±0.5
14	23	3RD ANGLE PROJECTION	
15	24	TITLE	
16	25	METAL BRACKET	
17	26	(for HWB18)	
18	27	REVISION	DRWG. NO.
19	28	A	868-066
20	29	OUTLINE	

