



- NOTES:  
 1. MATERIAL: COPPER C1100, TIN PLATED  
 2. UNLESS OTHERWISE NOTED, BURR SHALL NOT EXCEED 10% OF THE RAW MATERIAL THICKNESS AT ANY LOCATION  
 3. PART TO BE CLEAN, DEGREASED, FREE OF CONTAMINATION

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [ ] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				

LTR	DATE	REVISION	CHK	APD
A	06/26/13	508674ERA-RELEASE FYUE		
B	07/10/13	508881ECA-THICKNESS 2.3 WAS 2.0 FYUE		

COPIES TO	MTRL SPEC		SEE NOTE	
1 9 18	FINISH		SEE NOTE	
2 10 19	DRW	FYUE	DATE	06/26/13
3 12 20	CHK		DATE	
4 13 21	APPD		DATE	
5 14 23	SCALE		2:1	
6 15 33	SUPER DR			
7 16 43	FINISH GOOD WT		GRAMS/PIECE	
8 17 53	TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)			
DIMENSION		0.5 - 3	UP TO OVER	UP TO OVER
TOLERANCE		+0.05	+0.05	+0.15
3RD ANGLE PROJECTION		TITLE 4 POSITION BUS BAR		
3RD ANGLE PROJECTION		- FLEX MIDI HOLDER		
3RD ANGLE PROJECTION		REVISION		
3RD ANGLE PROJECTION		DRWG. NO.		
3RD ANGLE PROJECTION		OL-882-267-004		

