

## Specification Status: Released

### Electrical Rating

**Voltage: 16V MAX**  
**Current: 60A MAX**

Chip Size: 5x12mm

Leads: Nickel 1/4H  
0.125mm nominal thickness


Tape: Polyester(White)  
13mm Width

Solder: Lead-free

Lot Marking Ink Color (Green)

#### Marking:

- Manufacturer's Mark
- XX W27 — Part Identification
- — Lot Identification



**TABLE I. DIMENSIONS:**

	A		B		C		D		E		F	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
mm:	20.9	23.1	4.9	5.3	0.6	0.8	4.1	5.8	4.1	5.8	3.9	4.1
in*:	(0.82)	(0.92)	(0.19)	(0.21)	(0.02)	(0.03)	(0.16)	(0.23)	(0.16)	(0.23)	(0.15)	(0.16)

\*Rounded off approximation

**TABLE II. PERFORMANCE RATINGS: As measured in Muller Kelvin Clips Model BU-75K.**

I HOLD	CURRENT TRIP LIMITS						TIME TO TRIP		REFERENCE RESISTANCE		ONE-HOUR POST-TRIP RESISTANCE		TRIPPED-STATE POWER DISSIPATION	
	AMPS AT 0°C HOLD		AMPS AT 25°C HOLD		AMPS AT 60°C HOLD		SECONDS AT 25°C, 13.5A TYP		OHMS AT 25°C MIN		OHMS AT 25°C MIN		WATTS AT 25°C, 16V TYP	
	TRIP	TRIP	TRIP	TRIP	TRIP	TRIP	MAX	MAX	MAX	MAX	MAX	MAX	MAX	
2.7	4.0	8.9	2.7	6.5	1.4	3.8	--	5	0.012	0.018	0.012	0.036	--	2.5

Agency Recognition: UL, TUV, CSA  
 Reference Document: PS300  
 Precedence: This specification takes precedence over documents referenced herein.  
 Effectivity: Reference documents shall be the issue in effect on the date of invitation for bid.  
 CAUTION: Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

### Materials Information

**ROHS Compliant**

Directive 2002/95/EC  
Compliant

**ELV Compliant**

Directive 2000/53/EC  
Compliant

**Pb-Free**





Expertise Applied | Answers Delivered

**PolySwitch®**  
**PTC Devices**  
**Overcurrent Protection Device**

**PRODUCT: VLP270F**

DOCUMENT: SCD25981  
REV LETTER: D  
REV DATE: JULY 26, 2016  
PAGE NO.: 2 OF 2

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.