

SE-325 NEUTRAL-GROUNDING-RESISTOR MONITOR SETTING

Substation Identification: _____

Secondary Voltage: _____

SE-325 Model Number and Serial Number: _____

Ground-Fault Trip Level

| CHECK ONE | GF SETTING |
|-------------------------------------|------------|
| <input type="checkbox"/> | 4 A |
| <input checked="" type="checkbox"/> | 2 A |
| <input type="checkbox"/> | 0.5 A |

Ground-Fault Trip Time

Setting: _____ seconds

Output Contact Mode of Operation

| CHECK ONE | MODE SETTING |
|-------------------------------------|------------------------|
| <input type="checkbox"/> | SH (Shunt Trip) |
| <input checked="" type="checkbox"/> | UV (Undervoltage Trip) |

Sensing Resistor

| CHECK ONE | MODEL |
|-------------------------------------|----------|
| <input type="checkbox"/> | ER-600VC |
| <input checked="" type="checkbox"/> | ER-5KV |
| <input type="checkbox"/> | ER-15KV |
| <input type="checkbox"/> | ER-25KV |
| <input type="checkbox"/> | ER-35KV |

RES

| CHECK ONE | NGR RESISTANCE |
|-------------------------------------|----------------|
| <input type="checkbox"/> | 100K |
| <input checked="" type="checkbox"/> | 20K |

Remote Indication

| CHECK ONE | MODEL |
|-------------------------------------|---|
| <input type="checkbox"/> | None |
| <input checked="" type="checkbox"/> | RK-13 Relay Interface Module |
| <input type="checkbox"/> | RK-302 Remote Indication and Reset Kit |
| <input checked="" type="checkbox"/> | RK-325 Remote Indication and Reset Assembly |
| <input type="checkbox"/> | RK-325I Remote Indication Assembly |

RES Trip Lvel (Vac)

For RES = 100K

Range is 100 to 2000 Vac

Setting: _____

For RES = 20K

Range is 20 to 400 Vac

Setting: _____

NGR Ratings

Current: _____ A

Voltage: _____ V

Current Transformer

| CHECK ONE | CT SIZE |
|-------------------------------------|-------------------------------------|
| <input type="checkbox"/> | CT200, 56 mm (2.2") Inner Diameter |
| <input checked="" type="checkbox"/> | CT200L, 89 mm (3.5") Inner Diameter |