




NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY
2. MATERIAL: BODY -- MAPEX UL94 -V0, BLACK
M8 x 1.25 STUD -- SAE1215/DIN 9SMn28/11SMn30 STEEL, ZINC PLATED
3. MAXIMUM MOUNTING TORQUE FOR M4 MOUNTING HOLES 10 N*M, 7.4 LBF*FT
4. MAXIMUM TORQUE FOR M8 STUD 8.9-13.3 LBF*FT, 12-18 N*m

METRIC
ASSEMBLY



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES									
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.									
© DENOTES CRITICAL CHARACTERISTICS.									
CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE									
ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS									
CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE									

2	STUD	1	EA
1	BODY	1	EA
NO	COMPONENT NO	DESCRIPTION	QTY/M
BILL OF MATERIAL			

COPIES TO		MATL SPEC		SEE NOTE 2								
1	9	18	FINISH									
2	10	19										
3	12	20										
4	13	21	DRW	PVN	DATE	03/21/12	SCALE	1 : 1				
5	14	23	CHK		DATE		SUPER DR					
6	15	33										
7	16	43	APPD		DATE		FINSH GOOD WT					
8	17	53				GRAMS/PIECE						
TOLERANCES UNLESS OTHERWISE SPECIFIED												
DIMENSION		UP TO		OVER		UP TO		OVER				
		0.5 - 3		3 - 6		6 - 30		30 - 120				
TOLERANCE		±0.1		±0.1		±0.2		±0.3				
3RD ANGLE PROJECTION									±0.5			
		TITLE							JUNCTION BLOCK			
									NON-FEED-THRU			
		REVISION							DRWG. NO.			
A		03/21/12		504524ERA- SEE ERN PVN					B		OL-JBPT5N01ZXB	
B		06/04/14		510557ERA, PVN, ADDED STEEL GRADE TO NOTE 2								