






THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
REV.	DESCRIPTION	DATE	DESIGNED	APPROVED
A	Initial Release	28-Jul-22	L.Dal Molin	M.Tinto



ELECTRICAL DIAGRAM



CHARACTERISTIC AND PRESCRIPTION

- Nominal voltage: 8V±32V
- Maximum continuous current: 150A
- Maximum current 1000A for 5 sec
- Maximum short time current 400A for 30 sec
- Tightening torque M10 nuts: 10 ± 1Nm
- Tightening torque M5 nuts: 6 ± 1Nm
- Handle with four step 90° ON-OFF / ON-OFF 360° rotate continuous

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.						
linear dimensions						
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3
angle (for range of lengths)						
up to 10		>10 50	>50 120	>120 400		
±1°30'		±1°	±0°30'		±0°15'	
	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL					
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL					
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE					
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
	NAME	DATE	 Littelfuse® Expertise Applied Answers Delivered			
DRAWN	L. Dal Molin	2 Apr 2019				
CHECKED	-	-				
	-	-				
	-	-				
FORM NO: CVP-PE40-0013 REV A			TITLE			
FIRST ANGLE PROJECTION			IGC-150 MANUAL KNOB TO			
			SIZE: A3	DWG. NO.	OUTLINE 1600	REV. A
DO NOT SCALE DRAWING			SCALE 1:1			SHEET 1 OF 1