






THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
REV.	DESCRIPTION	DATE	DESIGNED	APPROVED
A	First issue of outline drawing	07-May-20	L.Dal Molin	M.Tinto



SCALE 1:1

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.									
linear dimensions									
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000			
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3			
angle (for range of lengths)									
up to 10		>10 50		>50 120		>120 400			
±1°30'		±1°		±0°30'		±0°15'			
 FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL									
<S> SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL									
CPK DENOTES CPK DIMENSIONS MINIMUM CPK VALUE									
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMANTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS									
CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE									
		NAME	DATE	 Littelfuse® Expertise Applied Answers Delivered					
DRAWN		L. Dal Molin	02-Apr-19						
CHECKED		-	-						
		-	-						
		-	-	TITLE EMERGENCY MANUAL BDS 300A					
FORM NO: CVP-PE40-0013 REV A									
FIRST ANGLE PROJECTION				SIZE: A3 DWG. NO. OL-08010100 OUTLINE REV. A					
 									
DO NOT SCALE DRAWING				SCALE 1:1			SHEET 1 OF 1		