



| PART NO. |
| --- |
| GDB61753Z |

| LTR | DATE | REVISION | CHK | APD |
| --- | --- | --- | --- | --- |
| A | 4/17/18 | 519180GCP - RELEASE MRY | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |






NOTES:

1. AGENCY INFORMATION:
   UL FILE NO. E309688
2. MATERIALS:
   INSULATOR-THERMOPLASTIC
   CONNECTOR-BRASS
3. TERMINATION:
   LINE: 8AWG-2/0
   LOAD: 4-14 AWG
4. RATINGS:
   600V
   MAXIMUM AMP PER POLE-175A
5. TORQUE:
   LINE: 35.5 IN-LB
   LOAD: 17.5 IN-LB

| | |
| --- | --- |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING. | |
| ● | DENOTES CRITICAL CHARACTERISTICS. |
| CPK | DENOTES CPK DIMENSIONS,-MINIMUM CPK VALUE |
| ⟨ST⟩ | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. |
| CP | DENOTES CP DIMENSIONS,-MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE. C |

| COPIES TO | MATL SPEC | | |
| --- | --- | --- | --- |
| 1 9 18<br>2 10 19<br>3 12 20<br>4 13 21<br>5 14 23<br>6 15 33<br>7 16 43<br>8 17 53 | FINISH | | |
| | DRW M YORK | DATE 4/9/18 | SCALE |
| | CHK | DATE | SUPER DR |
| | APPD | DATE | RAW STK WT LBS/M |

TITLE
GDB6175 SERIES DISTRIBUTION BLOCK OUTLINE

Littelfuse®
CHICAGO, ILLINOIS 60631

| REVISION | DRWG. NO. | FINAL |
| --- | --- | --- |
| A | OL-GDB6175 | |

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED