






REV.		DESCRIPTION	DATE	DESIGNED	APPROVED
A		FIRST ISSUE OF OUTLINE DRAWING	07-July-2020	Gasparini	Tinto



#### ELECTRICAL CHARACTERISTICS

- Nominal operating voltage: 12 ÷ 24 V
- Max continuous current on main contacts: 250 A
- Max current on main contacts short duration: 2000 A for 30 sec.

#### MECHANICAL CHARACTERISTICS


- Number of electrical and mechanical operations: 100.000
- Max locking torque nuts M12: 22 ± 1 Nm
- Max locking torque nuts M5: 1.6 ± 0.4 Nm

#### PRESCRIPTIONS

- (\*): Data of production
- We suggests to fix the device to the structure by screws M8 UNI 5931:1984 and plane washers 8.4 x 17 UNI 6592:1969 under head

SAP drawing number:

Material and treatments:

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.					
linear dimensions					
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000
±0,2	±0,3	±0,5	±0,8	±1,2	±2
angle (for range of lengths)					
up to 10	>10 50	>50 120	>120 400	>400 1000	>1000 2000
±1°30'	±1°	±0°30'	±0°15'		
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL				
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL				
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE				
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS				
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE				
	NAME	DATE			
DRAWN	L. Dal Molin	27/05/2019			
CHECKED	-	-			
	-	-			
	-	-			
FORM NO. CVP-PE40-0013 REV A		TITLE			
FIRST ANGLE PROJECTION		GENERAL ELECTRICAL MAIN SWITCH			
		TGC/RMSM 12 V SEP (+0-)			
DO NOT SCALE DRAWING		SIZE: A2	DWG. NO. OL-08097161	OUTLINE REV. A	
SCALE 1:1		SHEET 1 OF 1			