


2

1




Mechanical Dimensions :

A	B	C	D	E
0.076" \pm 0.008" (1.9304 \pm 0.2032mm)	0.049" \pm 0.008" (1.2446 to 0.2032 mm)	0.055" Max (1.397 Max)	0.008" Min (2X) (0.2032mm Min (2X))	Solder Plated Terminations Ends

Electrical Specifications :

Resistance (25 °C) Ω	Resistance Tolerance, $\pm\%$	Temp, Coefficient (%/ °C)	Beta(K)	Temp Rating(°C)	Power Rating(V)	Packaging
100 to 100000	1 to 10	3.31 to 4.4	2000~5000	-55~ +150	300~400	Tape & Reel

Rev	Description	By	Date	ECO NO
A	Initial Release	RKM	04/04/2023	
Revision History				
Reference Legacy No.		USPxxxx REV x		

Project Code XXXXXX			
 Third Angle Projection			
Units Inch(mm)	Division IBU - Temperature Sensors		
General Tolerances 0.X = \pm 0.X 0.XX = \pm 0.XX 0.XXX = \pm 0.XXX	Title End Banded NTC Thermistor Chips-0805		
Drawn By RKM	Finished Product Part Number NSKR		Rev A
Date 04/04/2023	Internal No. NSKR	Size A	Sheet 1 of 1
		Do Not Scale	

2

1