





| LTR | DATE     | REVISION           | CHK | APD |
|-----|----------|--------------------|-----|-----|
| A   | 04/19/11 | 502069ERA-RELEASED | OPL |     |



DETAILS ARE SHOWN WITH COVERS REMOVED



NOTES:

1. DURING FINAL ASSEMBLY. HEX NUTS ARE INITIALLY PROVIDED FINGER TIGHTENED ONLY
2. MATERIAL:  
COVER - COVER: TPV 251-80W232  
BASE: AMODEL 6133 V0, BLACK  
STUDS & NUTS - M8 X 1.25 STEEL, ZINC PLATED WITH TRIVALENT CHROMATE, LEACHED AND SEALED, INTEGRAL TORQUE CONTROL LUBRICANT FINISH (MEETS 96 HR. ASTM STD. B-117 SALT SPRAY REQ.)
3. NO FUSE RATING INCLUDED
4. TEMPERATURE RATING: -40°C TO 125°C

| NO   | COMPONENT NO  | DESCRIPTION                  | QTY/M  | U/M      |           |
|--|---|------------------------------|--------|----------|-----------|
| BILL OF MATERIAL   |   |                              |        |          |           |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.     |   |                              |        |          |           |
| DIMENSIONS IN BRACKETS ( ) ARE INCHES                          |   |                              |        |          |           |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING. |   |                              |        |          |           |
| ⊙  | DENOTES CRITICAL CHARACTERISTICS.   |                              |        |          |           |
| CPK  | DENOTES CPK DIMENSIONS. -MINIMUM CPK VALUE  |                              |        |          |           |
| ST   | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS |                              |        |          |           |
| CP   | DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE               |                              |        |          |           |
| COPIES TO  |   | MATERIAL SPEC                |        |          |           |
| 1  | 9   | 18                           |        |          |           |
| 2  | 10  | 19                           | FINISH |          |           |
| 3  | 12  | 20                           |        |          |           |
| 4  | 13  | 21                           | DRW    | OPL      |           |
| 5  | 14  | 23                           | DATE   | 04/05/11 |           |
| 6  | 15  | 33                           | SCALE  | 1:1      |           |
| 7  | 16  | 43                           | CHK    | DATE     |           |
| 8  | 17  | 53                           | APPD   | DATE     |           |
| TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MK1)      |   |                              |        |          |           |
| DIMENSION  | 0.5 - 3   | 3 - 6                        | 6 - 30 | 30 - 120 | 120 - 400 |
| TOLERANCE  | +0.1  | +0.1                         | +0.2   | +0.3     | +0.5      |
| 3RD ANGLE PROJECTION   |   |                              |        |          |           |
| TITLE  |   | 3 POLE FLEX-MEGA FUSE HOLDER |        |          |           |
| REVISION   |   | DRWG. NO.                    |        | OUTLINE  |           |
| A  |   | OL-02983002ZXC               |        |          |           |

METRIC



REV. 01/08/11  
OL-02983002ZXC

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED