




DOVETAIL FEATURES
USED TO INTERLOCK
MULTIPLE HOLDERS



- NOTES:
- 1) BASE: UL94V-0 GLASS-FILLED PPA
M8 STUDS: ZINC-PLATED STEEL
COVER: UL94V-0 ELASTOMER
 - 2) MAX FUSE RATING: 500A
 - 3) M8 STUD TORQUE: 12-18Nm
MOUNTING TORQUE (W/M6 BOLTS & WASHERS): 5Nm
 - 4) TEMPERATURE RATING: -40°C TO 125°C
 - 5) WIRE SIZE: 8mm² TO 30mm²



METRIC

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES					
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.					
⊙	DENOTES CRITICAL CHARACTERISTICS.				
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE				
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS				
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE				

COPIES TO		MATL SPEC		SEE NOTES	
1	9	18	FINISH	N/A	
2	10	19	DRW	OPL	DATE 10/27/11
3	12	20	CHK	DATE	SCALE 1:2
4	13	21	APPD	DATE	SUPER DR
5	14	23	TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)		
6	15	33	DIMENSION		
7	16	43	TOLERANCE		
8	17	53	3RD ANGLE PROJECTION		
TITLE		FLEX-MEGA ASSY WITHOUT HARDWARE		REVISION DRWG. NO.	
FLEX-MEGA ASSY WITHOUT HARDWARE		B		OL-02981037HXFC-0	
LITTELFUSE		DES PLAINES, ILLINOIS 60016			