



**NOTES:**  
 1. MATERIAL:  
 BASE: UL94V-0 GLASS FILLED NYLON  
 STUDS: M5  
 NUTS: ZINC-PLATED NYLOCK NUT  
 2. TORQUE RATING: 5±1 Nm  
 3. FUSE RATING: 30-200A  
 4. WIRE SIZE: 14-4 AWG (2.5mm<sup>2</sup>-20mm<sup>2</sup>)  
 5. TEMPERATURE RATING: -40°C TO 125°C

**PACKAGING NOTES:**  
 1. PARTS ARE PACKED 50 PC PER BAG, 10 BAGS PER BOX.

**METRIC**  
 ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [ ] ARE INCHES.  
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

☉ DENOTES CRITICAL CHARACTERISTICS.  
 CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE  
 ☞ DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS  
 CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

**BILL OF MATERIAL**

| LTR  |       | DATE     |          | REVISION                                |                | CHK  | APD   |
|--|-------|----------|----------|---|----------------|------|-------|
| A  |       | 05/16/11 |          | 502090ERA-RELEASE                       | OPL            |      |       |
| COPIES TO  |       |          |          |   |                |      |       |
| 1  | 9     | 18       |          |   |                |      |       |
| 2  | 10    | 19       |          |   |                |      |       |
| 3  | 12    | 20       |          |   |                |      |       |
| 4  | 13    | 21       |          |   |                |      |       |
| 5  | 14    | 23       |          |   |                |      |       |
| 6  | 15    | 33       |          |   |                |      |       |
| 7  | 16    | 43       |          |   |                |      |       |
| 8  | 17    | 53       |          |   |                |      |       |
| MATERIAL SPECIFICATION                                   |       |          |          |   |                |      |       |
| FINISH   |       |          |          |   |                |      |       |
| DRW  | OPL   | DATE     | 05/16/11 | SCALE                                   | 1:1            |      |       |
| CHK  |       | DATE     |          |   | SUPER DR       |      |       |
| APPD   |       | DATE     |          |   | FINISH GOOD WT |      |       |
| TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mk) |       |          |          |   |                |      |       |
| DIMENSION  | UP TO | OVER     | UP TO    | OVER                                    | UP TO          | OVER | UP TO |
|  | 0.5   | - 3      | 3        | - 6                                     | 6              | - 30 | 30    |
| TOLERANCE  | ±0.1  |          | ±0.1     |   | ±0.2           |      | ±0.3  |
| 3RD ANGLE PROJECTION                                     |       |          |          |   |                |      |       |
|  |       |          |          |   |                |      |       |
| TITLE  |       |          |          | BASE FOR MIDI INLINE HOLDER, W/M5 BOLTS |                |      |       |
| REVISION   |       |          |          | DRWG. NO.                               |                |      |       |
| A  |       |          |          | OL-498921-2                             |                |      |       |
| OUTLINE  |       |          |          | OUTLINE                                 |                |      |       |
|  |       |          |          |   |                |      |       |
| DES. PLAINES, ILLINOIS 60016                             |       |          |          |   |                |      |       |