

NOTES: (UNLESS OTHERWISE SPECIFIED)

1. ASSOCIATED CAD FILE DEFINES ALL NONDIMENSIONED FEATURES

2. PRODUCT WEIGHT: 0.18 Kg

3. MAXIMUM TERMINAL STUD TORQUE: 13.56 NM (120IN-LB)

4. FRONT PANEL MOUNT IN 67MM (2-5/8") HOLE

5. TERMINAL HARDWARE: 3/8"-16 NUT SERRATED FLANGE, STAINLESS STEEL

6. REAR PANEL MOUNT IN 60MM [2-3/8"] HOLE






7. REAR PANEL MOUNT HEX FEATURE FOR #10 NUTS

8. ELECTRICAL SPECIFICATOIN:
- MAX OPERATING VOLTAGE: 32V DC
- MAX CONTINUOUS CURRENT: 300A
- CRANKING RATING (30 SEC) (1X4/0 CABLE): 1,250A

9. INGRESS RATING: IP67 & IP69K

10. IGNITION PROTECTION: MEETS ISO 8846 7 SAE J1171

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	Per EC# 515700: INITIAL RELEASE	3/22/2016	J. LIU
	B	PER EC#515935: ADDED A PERPENDICULARITY CALLOUT	5/26/2016	J. LIU



DIMENSIONS ARE IN MM.		DRAWN		NAME		DATE			
DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI / ASME Y14.5M-1994		J. LIU		11/15/2013				805 W. ORCHARD DR., STE. 6, BELLINGHAM, WA 98225 Phone (360)738-9010 Fax (360)738-0372	
THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.		CHECKED		-		-		Switch Master Panel Mt	
		-		-		-			
		-		-		-			
		-		-		-			
		THIRD ANGLE PROJECTION						SIZE DWG. NO.	
								OL-880062	
						SCALE 1:1		REV. B	
								SHEET 1 OF 1	