



METRIC
COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
◎	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

LTR	DATE	REVISION	CHK	APD
A	20/Oct/18	516562GCC-NEW RELEASE FYUE		
B	16/Oct/17	517965GCC-DELETE DIMENSION 6.9 FYUE		

COPIES TO	MATL SPEC
1 9 18	2.0mm MS PLATE
2 10 19	FINISH
3 12 20	ZINC CHROMATE PLATED (t = 3-8 microns)
4 13 21	DRW FYUE
5 14 23	DATE 20/Oct/16
6 15 33	CHK
7 16 43	DATE
8 17 53	APPD
	DATE
	FINISH GOOD WT
	GRAMS/PIECE
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)	
DIMENSION	UP TO OVER UP TO OVER UP TO OVER
	0.5 - 3 3 - 6 6 - 30 30 - 120 120 - 400
TOLERANCE	+0.1 ±0.1 ±0.2 ±0.3 ±0.5
3RD ANGLE PROJECTION	
TITLE	
METAL BRACKET	
(for HWB18,12&6)	
REVISION	DRWG. NO.
B	868-068
OUTLINE	

LIPA CITY, BATANGAS, PHILIPPINES	