CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED

PART NO.
GDB63101Z

NOTES:


1. AGENCY INFORMATION:
   UL FILE NO. E309688


2. MATERIALS:
   INSULATOR-THERMOPLASTIC
   CONNECTOR-BRASS


3. TERMINATION:
   LINE: 3/0-350MCM
   LOAD: (2) 2-14 AWG
   (5) 6-14 AWG
   (4) 8-14 AWG


4. RATINGS:
   600V
   MAXIMUM AMP PER POLE-310A

5. TORQUE:
   LINE: 230 IN-LB
   LOAD: 2-14AWG 31 IN-LB
   6-14 AWG 18 IN-LB
   8-14 AWG 18 IN-LB









ITEM NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

BILL OF MATERIAL

MATL SPEC	FINISH
	NONE

DRW	DATE	SCALE
M YORK	4/9/18	
CHK	DATE	SUPER DRW
APPD	DATE	RAW STK WT LBS/M

COPIES TO
1 9 18
2 10 19
3 12 20
4 13 21
5 14 23
6 15 33
7 16 43
8 17 53

TITLE
GDB6310 SERIES DISTRIBUTION BLOCK OUTLINE

Littelfuse®
CHICAGO, ILLINOIS 60631

REVISION A
DRWG. NO. DL-GDB6310

LTR	REVISION	CHK	APD
A	519180GCP - RELEASE 4/17/18 MRY		

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

● DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS,-MINIMUM CPK VALUE

(ST) DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.

CP DENOTES CP DIMENSIONS,-MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.