



NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY
2. MATERIAL: BODY -- MAPEX UL94 -V0, BLACK
M8 x 1.25 STUD -- SAE1215/DIN 95Mn28/11SMn30 STEEL, ZINC PLATED
3. MAXIMUM MOUNTING TORQUE FOR M4 MOUNTING HOLES 10 N*M, 7.4 LBF*FT
4. MAXIMUM TORQUE FOR M8 STUD 8.9-13.3 LBF*FT, 12-18 N*m

METRIC
ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊙	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

2	STUD	1	EA
1	BODY	1	EA
NO	COMPONENT NO	DESCRIPTION	QTY/M

BILL OF MATERIAL

COPIES TO	MATL SPEC	SEE NOTE 2
1 9 18	FINISH	
2 10 19	DRW	PVN
3 12 20	DATE	03/21/12
4 13 21	CHK	SCALE
5 14 23	DATE	SUPER DR
6 15 33	APPD	FINISH GOOD WT
7 16 43		GRAMS/PIECE
8 17 53		

DIMENSION	UP TO	OVER	UP TO	OVER	UP TO	OVER
0.5 - 3	3	6	30	30	120	120
TOLERANCE	±0.1	±0.1	±0.2	±0.3	±0.5	±0.5

TITLE	JUNCTION BLOCK
3RD ANGLE PROJECTION	NON-FEED-THRU
REVISION	DRWG. NO.
B	OL-JBPT5N01ZXB

