



treatments:	<table><tr><td>CHECKED</td><td>-</td><td>-</td><td>-</td></tr><tr><td></td><td>-</td><td>-</td><td>-</td></tr><tr><td></td><td>-</td><td>-</td><td>-</td></tr><tr><td></td><td>-</td><td>-</td><td>-</td></tr></table>			CHECKED	-	-	-		-	-	-		-	-	-		-	-	-	Expertise Applied Answers Delivered		
	CHECKED	-	-	-																		
		-	-	-																		
		-	-	-																		
	-	-	-																			
	<table><tr><td colspan="4">FORM NO.: CVP-PE40-0013 REV A</td></tr><tr><td colspan="4">FIRST ANGLE PROJECTION</td></tr><tr><td></td><td></td><td colspan="2"></td></tr></table>			FORM NO.: CVP-PE40-0013 REV A				FIRST ANGLE PROJECTION								TITLE 250A MANUAL BATTERY MASTER SWITCH WITH FIXED HANDLE SIZE: A2						
FORM NO.: CVP-PE40-0013 REV A																						
FIRST ANGLE PROJECTION																						
																						
	<table><tr><td>DO NOT SCALE DRAWING</td><td>SCALE 1:1</td><td> OUTLINE REV OL-08099161 </td><td> C </td></tr></table>			DO NOT SCALE DRAWING	SCALE 1:1	OUTLINE REV OL-08099161	C	SHEET 1 OF 1														
DO NOT SCALE DRAWING	SCALE 1:1	OUTLINE REV OL-08099161	C																			

		DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.						
linear dimensions								
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000		
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3		
angle (for range of lengths)								
up to 10		>10 50	>50 120	>120 400				
±1°30'		±1°	±0°30'	±0°15'				
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL							
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL							
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE							
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS							
CP	DENOTES CP DIMENSIONS, MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE							
		NAME		DATE		 Expertise Applied Answers Delivered		
DRAWN		L. Dall Molin		22-Jan-21				
CHECKED		-		-				
		-		-				
		-		-				
FORM NO: CVP-PE40-0013 REV A		TITLE						
FIRST ANGLE PROJECTION		250A MANUAL BATTERY MASTER						
		SWITCH WITH FIXED HANDLE						
		SIZE: A2		DWG. NO.		OUTLINE REV. C		
DO NOT SCALE DRAWING		SCALE 1:1					SHEET 1 OF 1	

CHARACTERISTICS

- Max operating voltage: 24 DC
- Max continuous current: 250A & 350A
- Intermittent current: 2500A at 3 sec.
- M10 nut closing pair: 19(±3) Nm
- M5 nut closing pair: 1.5(±0.5) Nm
- Locking nut M30x1.5: 35(±5) Nm
- Maximum thickness lockable with nut M30: 12mm
- Handle operating torque: 2±0.5 Nm

Material and treatments: