


| PART NUMBER |
|-------------|
| OLD14401Z |
| OLD14402Z |
| OLD14403Z |
| OLD14404Z |


| REVISION | | |
|----------|----------|---|
| REV | DATE | DESCRIPTION |
| A | 12/11/17 | 516515GCP - RELEASE PER EM2988 MRY |
| B | 1/5/22 | 524659ECP/D - CORRECT PART NUMBERS IN CHART MRY |





- NOTES:
1. AGENCY INFORMATION
UL FILE NO. E171395
CSA FILE NO. LR700111
 2. MATERIALS:
INSULATOR BASE: THERMOPLASTIC
CONNECTOR: ALUMINUM, TIN PLATED
 3. TERMINATION:
LINE: (1) #2-14 AWG
LOAD: (4) #10-18 AWG
 4. MAXIMUM AMP RATING PER POLE: 115A
 5. TORQUE:
LINE: #2 AWG 5.6 Nm (50 IN-LB)
#4-6 AWG 5.1 Nm (45 IN-LB)
#8 AWG 4.5 Nm (40 IN-LB)
#10-14 AWG 4 Nm (35 IN-LB)

LOAD: #10-18 AWG 0.8 Nm (7 IN-LB)

TOLERANCE (UNLESS OTHERWISE SPECIFIED):
1 PLACE ± 2.5mm [0.10]
2 PLACE ± 0.76mm [0.03]
3 PLACE ± 0.381mm [0.015]



DETAIL "A"
PRODUCT LABEL

| | | | |
|---|--|---------------|----------------------------|
| ● | DENOTES CRITICAL CHARACTERISTICS. | | |
| CPK | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE | | |
| (ST) | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. | | |
| CP | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE. | | |
| MATL SPEC | | FINISH | |
| DRW MYORK | DATE 10/16/2017 | SCALE NTS | FINISH GOOD WT GRAMS/PIECE |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994 | | | |
| 3RD ANGLE PROJECTION | | | |
|  | | | |
| TITLE | | | |
| OLD1440 SERIES DISTRIBUTION BLOCK OUTLINE | | | |
|  Littelfuse® CHICAGO, ILLINOIS 60631 | | REVISION B | DRWG NO. OL-LD1440 |
| | | | SHEET 1 OF 1 |