

NOTES: (UNLESS OTHERWISE SPECIFIED)

1. ASSOCIATED CAD FILE DEFINES ALL NONDIMENSIONED FEATURES

2. PRODUCT WEIGHT: 0.22 Kg

3. MAXIMUM TERMINAL STUD TORQUE: 13.56 NM (120IN-LB)

4. PAD LOCK HOLE FOR LOCKOUT IN OFF POSITION

5. FRONT PANEL MOUNT IN 67MM (2-5/8") HOLE






6. TERMINAL HARDWARE: 3/8"-16 NUT SERRATED FLANGE, STAINLESS STEEL

7. ELECTRICAL SPECIFICATOIN:

- MAX OPERATING VOLTAGE: 32V DC
- MAX CONTINUOUS CURRENT: 300A
- CRANKING RATING (30 SEC) (1X4/0 CABLE): 1,250A

8. INGRESS RATING: IP67 & IP69K

9. IGNITION PROTECTION: MEETS ISO 8846 7 SAE J1171



REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	Per EC# 515700: INITIAL RELEASE OUTLINE DRAWING	3/22/2016	J. Liu
	B	PER EC#515935: ADDED A PERPENDICULARITY CALLOUT	5/26/2016	J. Liu

DIMENSIONS ARE IN MM.

DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI / ASME Y14.5M-1994

THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

NAME			DATE
DRAWN	J. Liu		3/22/2016
CHECKED	-		-
-	-		-
-	-		-
-	-		-
THIRD ANGLE PROJECTION			

		805 W ORCHARD DR. STE 6, BELLINGHAM, 98225 Phone (360)738-9010 Fax (360)738-0372	
Switch Master On-Off Panel Mount, Lock Out		REV. B	
SIZE C	DWG. NO. OL-880064	SHEET 1 OF 1	
SCALE 1:1			