

**SPECIFICATIONS:**

**VOLTAGE RATING:** 600VAC / 1000VDC

**AMP RATING:** 30 AMPERES



**INTERRUPT RATING:** 20kA AC / 50kA DC

**WIRE RANGE:** #8-14 AWG STRANDED Cu ONLY UL CLASS B & CLASS C WIRE  
#10-14 AWG SOLID Cu ONLY

**SUGGESTED TORQUE:** 2 N-m [17.7 IN-LB]

**APPROVALS:** AC: UL RECOGNIZED (FILE NO. E14721)  
CSA CERTIFIED (FILE NO. LR7316)  
DC: LITTELFUSE SELF CERTIFIED

| REVISION |         |   |
|----------|---------|---|
| REV      | DATE    | DESCRIPTION                                     |
| A        | 10/3/22 | 525720GCP - RELEASE MRY                         |
| B        | 11/8/22 | 525898ECP/D - CHANGE TOLERANCE & WIRE RANGE MRY |

|   |  |               |                               |              |
|---|--|---------------|-------------------------------|--------------|
| 1   |  |               |                               |              |
| NO  | COMPONENT NO   | DESCRIPTION   | QTY/M                         | U/M          |
| BILL OF MATERIAL  |  |               |                               |              |
| <S>   | CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE   |               |                               |              |
| ●   | DENOTES CRITICAL CHARACTERISTICS.  |               |                               |              |
| CPK   | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE   |               |                               |              |
| ⌞ST⌟  | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. |               |                               |              |
| CP  | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.               |               |                               | B            |
| MATL SPEC   |  | FINISH        |                               |              |
| DRW<br>JMOLER   | DATE<br>9/28/2022  | SCALE<br>NTS  | FINISH GOOD WT<br>GRAMS/PIECE |              |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994 |  |               |                               |              |
| 3RD ANGLE<br>PROJECTION<br>  |  |               |                               |              |
| TITLE<br>LPHV004 OUTLINE  |  |               |                               |              |
|  <b>Littelfuse®</b><br>CHICAGO, ILLINOIS 60631   |  | REVISION<br>B | DRWG NO.<br>OL-LPHV004        | SHEET 1 OF 1 |