




SCALE 1:2



REVISIONS

REV.	DESCRIPTION	DATE	DESIGNED	APPROVED
A	First issue of outline drawing	19-May-20	L.Dal Molin	M.Tinto

3	Knob complete		1	EA
2	Upper body	Polyamide	1	EA
1	Lower body comoulded		1	EA
POS.	DESCRIPTION	MATERIAL	Q.TY	U/M

CHARACTERISTICS:

- Number of mechanical operations: 5000
- Number of electrical operations: 5000
- Rated voltage: 12V-24V
- Maximum continuous current: 150A
- Maximum current: 1200A for 5s at 25°C
- Fixing on support with screws and nuts M6- tightening torque 3.3 ± 0.2 Nm ; fixing the knob to the body with self-tapping screws - tightening torque 0.5 ± 0.1 Nm

OPERATION

- To close the contacts: press the button for at least 1mm and rotate clockwise for 90°; release the button checking that it returns to the previous position and the indicator is in the ON position
- To open the contacts: press the button firmly for at least 1mm; release immediately checking that the indicator is in the OFF position

SAP drawing number:

Material and treatments:

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.						
linear dimensions						
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3
angle (for range of lengths)						
up to 10	>10 50	>50 120	>120 400			
±1°30'	±1°	±0°30'	±0°15'			
	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL					
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL					
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE					
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
	NAME	DATE	 Littelfuse® Expertise Applied Answers Delivered			
DRAWN	L. Dal Molin	19-May-20				
CHECKED	-	-				
	-	-				
	-	-				
FORM NO: CVP-PE40-0013 REV A			TITLE			
FIRST ANGLE PROJECTION			MANUALE BDS IGC/175-P			
			SIZE:	SIZE:	OUTLINE	REV.
			A3	OL-08080200	A	
DO NOT SCALE DRAWING			SCALE 1:1		SHEET 1 OF 1	