



CAD GENERATED DRAWING – NO PENCIL CHANGES ALLOWED

PART NO.	FIGURE	A	B	C	D	E	F	G	H	J	K	L	M	MAX. TORQUE (in-lb/N-m)	MAX. CURRENT RATING (AMPS)	WEIGHT	COLOR
JBPT3P01ZXB	1	52.4 (2.06)	23.8 (0.94)	17.5 (0.69)	22.2 (0.87)	17.5 (0.69)	7.9 (0.31)	23.8 (0.94)	1.6 (0.06)	1.6 (0.06)	33.3 (1.31)	5.6(0.22) dia. hole w/ 10.4(0.41) dia. C'bore x 3.6(0.14) deep	3/8-16	150 (17)	250	68.8g	BLACK
JBPT3P02ZXB	1	52.4 (2.06)	22.2 (0.87)	15.9 (0.63)	15.9 (0.63)	28.6 (1.13)	7.9 (0.31)	23.8 (0.94)	1.6±0.15 (0.06)	1.6±0.15 (0.06)	33.3 (1.31)	5.6(0.22) dia. hole w/ 10.4(0.41) dia. C'bore x 3.6(0.14) deep	3/8-16	150 (17)	250	80.5g	BLACK
JBPT3N03ZXB	2	54.0 (2.06)	24.9 (0.98)	15.9 (0.63)	22.2 (0.87)	17.5 (0.69)	7.9 (0.31)	None	1.6 (0.06)	None	34.9 (1.37)	5.6(0.22) dia. hole w/ 9.4(0.37) dia. C'bore x 3.6(0.14) deep	3/8-16	150 (17)	250	43.7g	BLACK
JBPT3N03ZXR	2	54.0 (2.06)	24.9 (0.98)	15.9 (0.63)	22.2 (0.87)	17.5 (0.69)	7.9 (0.31)	None	1.6 (0.06)	None	34.9 (1.37)	5.6(0.22) dia. hole w/ 9.4(0.37) dia. C'bore x 3.6(0.14) deep	3/8-16	150 (17)	250	43.7g	RED
JBPT3N04ZXB	2	54.0 (2.06)	24.9 (0.98)	15.9 (0.63)	22.2 (0.87)	17.5 (0.69)	7.9 (0.31)	None	1.6 (0.06)	None	34.9 (1.37)	5.6(0.22) dia. hole w/ 9.4(0.37) dia. C'bore x 3.6(0.14) deep	M8*1.25	150 (17)	250	43.7g	BLACK
JBPT3N04ZXR	2	54.0 (2.06)	24.9 (0.98)	15.9 (0.63)	22.2 (0.87)	17.5 (0.69)	7.9 (0.31)	None	1.6 (0.06)	None	34.9 (1.37)	5.6(0.22) dia. hole w/ 9.4(0.37) dia. C'bore x 3.6(0.14) deep	M8*1.25	150 (17)	250	43.7g	RED



METRIC

ASSEMBLY

FIGURE





FIGURE 2



- NOTES:
1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
 2. MATERIAL: BODY-> THERMOPLASTIC, PA66
STUD-> STEEL Zn Plated
 3. MAXIMUM MOUNTING TORQUE 45 IN.LBS (5 N-m).
 4. TEMPERATURE RATING: -40°C TO 125°C

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

© DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS. -MINIMUM CPK VALUE

ST
DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS

CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

[illegible]