


PART NUMBER	CONNECTOR
OFHMO200Z	YES - BUTT SPLICE
OFHMO200Z-NC	NO CONNECTOR

LTR	DATE	REVISION	CHK	APD
A	01/28/14	510055ECA-NEW RELEASED FYUE		



NOTE:
1. THIS IN-LINE FUSEHOLDER IS DESIGNED TO TURN ONE SLOT INTO TWO.
2. MAX. INSTALLATION RATING UP TO 10 AMPS.
3. BUTT SPLICE CONNECTORS PULL-OUT FORCE IS 15KGF MIN. (FOR OFHMO200Z ONLY)
4. MAX. FUSE INSERTION FORCE TO BE 15KGF.
5. FUSE PULL OUT FORCE TO BE 3.5 - 7.0KGF.

-								
-								
-								
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M				
BILL OF MATERIAL								
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES								
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.								
⊙	DENOTES CRITICAL CHARACTERISTICS.							
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE							
⬢ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS							
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE							
COPIES TO		MATL SPEC						
1	9	18	FINISH					
2	10	19						
3	12	20						
4	13	21						
5	14	23	DRW	FYUE	DATE	01/28/14	SCALE	2:1
6	15	33	CHK		DATE		SUPER DR	
7	16	43	APPD		DATE		FINSH GOOD WT	
8	17	53			GRAMS/PIECE			
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)								
DIMENSION	0.5 - 3	UP TO 3 OVER 3 - 6	UP TO 6 OVER 6 - 30	UP TO 30 OVER 30 - 120	UP TO 120 OVER 120 - 400			
TOLERANCE	±0.1	±0.1	±0.2	±0.3	±0.5			
3RD ANGLE PROJECTION	TITLE							
⊙	MINI ADD-A-CIRCUIT							
Littelfuse®		REVISION		DRWG. NO.		OUTLINE		
		A		OL-OFHMO200Z				
DES PLAINES, ILLINOIS 60016								

METRIC
ASSEMBLY

Littelfuse
DES PLAINES, ILLINOIS 60016

REVISION
A

DRWG. NO.
OL-OFHMO200Z

OUTLINE

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED