



PART NUMBER	"A"	"B"	"C"	"D"	LEAD "A" COLOR	LEAD "B" COLOR	WIRE SIZE
FHAC0001ZXJ	89.5±5 [3.524]	89.5±5 [3.524]	6.35±2 [0.25]	6.35±2 [0.25]	BLACK	BLACK	16 AWG
FHAC0001ZXJA	89.3±5 [3.516]	89.3±5 [3.516]	6.35±2 [0.25]	6.35±2 [0.25]	RED	RED	16 AWG
FHAC0001ZXJB	287.7±5 [11.325]	287.7±5 [11.325]	6.35±2 [0.25]	6.35±2 [0.25]	BLACK	BLACK	16 AWG
FHAC0001ZXJC	89.3±5 [3.516]	89.3±5 [3.516]	6.35±2 [0.25]	6.35±2 [0.25]	BLUE	BLUE	16 AWG
FHAC0001ZXJD	237.7±5 [9.358]	237.7±5 [9.358]	6.35±2 [0.25]	6.35±2 [0.25]	RED	RED	16 AWG
FHAC0001ZXJE	241.7±5 [9.516]	241.7±5 [9.516]	6.35±2 [0.25]	6.35±2 [0.25]	BLACK	BLACK	16 AWG
FHAC0001ZXJF	101.7±5 [4.240]	917.7±5 [36.130]	6.35±2 [0.25]	6.35±2 [0.25]	RED	RED	16 AWG
FHAC0001ZXJG	155.0±5 [6.102]	155.0±5 [6.102]	18.0±2 [0.709]	18.0±2 [0.709]	BLACK	BLACK	16 AWG
FHAC0001ZXJH	89.5±5 [3.524]	89.5±5 [3.524]	6.35±2 [0.25]	6.35±2 [0.25]	YELLOW	YELLOW	16 AWG
FHAC0001ZXJJ **	1325±20 [52.165]	125±5 [4.921]	-	-	RED	RED	FLR2X-B 0.5MM2
FHAC0001ZXJK	200.0±5 [7.874]	200.0±5 [7.874]	6.35±2 [0.25]	6.35±2 [0.25]	BLACK	BLACK	16 AWG
FHAC0001ZXJL	450.0±5 [17.716]	200.0±5 [7.874]	-	-	RED	RED	FLRY-A 1.5MM2
FHAC0001ZXJM	89.5±5 [3.524]	89.5±5 [3.524]	12.7±2 [0.50]	12.7±2 [0.50]	BLACK	BLACK	16 AWG


** NOTE: THIS MODEL MUST BE SHIPPED WITH 3A ATOF FUSE



- NOTES:
- HOLDER MATERIAL: BLACK TPV
 - CONTACTS: COPPER ALLOY: TIN-PLATED
 - WIRE: STRANDED COPPER, GXL/FLR2X-B (125°C RATED), FLRY-A (105°C RATED) (SEE CHART FOR WIRE SIZE)
 - CRIMP: MUST MEET SAE/USCAR 21 STANDARD
 - RATING: MAX. 20A, 32Vdc (10A FOR FHAC0001ZXJJ)
 - MAX TEMPERATURE 105°C
 - FUSEHOLDER SHOULD NOT BE PLACED UNDER TENSION IN FINAL APPLICATION.

METRIC
ASSEMBLY

LTR	DATE	REVISION	CHK	APD
A	06/20/07	63273 - RELEASED DHM		
B	10/05/07	000175ER-RELEASED FHAC0001ZXJA THRU FHAC0001ZXJF DHM		
C	11/29/07	000227ER-RELEASED FHAC0001ZXJG DHM		
D	05/13/13	508317ERA-RELEASE FHAC0001ZXJH FYUE		
E	01/29/14	509986ERA-RELEASE FHAC0001ZXJJ		
F	05/20/14	510513ECA-CHANGE WIRE OF FHAC0001ZXJJ		
G	04/30/15	511837ECA-REMOVE MODEL NAME OF HOLDER MATERIAL FYUE		
H	07/Sep/15	514861GCA-RELEASE FHAC0001ZXJK FYUE		
J	05/Jan/17	517047GCC-RELEASE FHAC0001ZXJL FYUE		
K	02/Mar/17	517170ECC-CHANGE SPEC OF FHAC0001ZXJL FYUE		
L	04/Jul/19	520979GCC-RELEASE FHAC0001ZXJM FYUE		

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES								
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.								
	DENOTES CRITICAL CHARACTERISTICS.							
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE							
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS							
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE							
COPIES TO		MATL SPEC						
		SEE NOTES						
1	9	18	FINISH					
2	10	19						
3	12	20						
4	13	21	SEE NOTES					
5	14	23	DRW	DHM	DATE	06/20/07	SCALE	1:1
6	15	33	CHK		DATE		SUPER DR	
7	16	43	APPD		DATE		FINISH GOOD WT	
8	17	53					GRAMS/PIECE	
TOLERANCE UNLESS OTHERWISE SPECIFIED								
ONE PLACE DEC +/- .3			THREE PLACE DEC +/- .100					
TWO PLACE DEC +/- .25			ANGULAR +/- 1°					
3RD ANGLE PROJECTION		TITLE						
		ATO IN-LINE FUSEHOLDER						
		REVISION		DRWG. NO.		OUTLINE		
DES PLAINES, ILLINOIS 60016		L		OL-FHAC0001ZXJ				

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED