



PART NO.
GDB60801Z


LTR	DATE	REVISION	CHK	APD
A	4/17/18	519180GCP - RELEASE MRY		











NOTES:

1. AGENCY INFORMATION:
   UL FILE NO. E309688

2. MATERIALS:
   INSULATOR-THERMOPLASTIC
   CONNECTOR-BRASS

3. TERMINATION:
   LINE: 8-14 AWG
   LOAD: (2) 8-4 AWG
   (4) 10-14 AWG

4. RATINGS:
   600V
   MAXIMUM AMP PER POLE-80A

5. TORQUE:
   LINE: 13.5 IN-LB
   LOAD: 8-4 AWG 13.5 IN-LB
   10-14 AWG 7.2 IN-LB

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.	
●	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS,-MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS,-MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE. C

COPIES TO		
1	9	18
2	10	19
3	12	20
4	13	21
5	14	23
6	15	33
7	16	43
8	17	53

MATL SPEC

FINISH

DRW M YORK	DATE 04/09/18	SCALE
CHK	DATE	SUPER DR
APPD	DATE	RAW STK WT LBS/M

TITLE
80A IEC DISTRIBUTION BLOCK OUTLINE

Littelfuse®
CHICAGO, ILLINOIS 60631

REVISION	DRWG. NO.	FINAL
A	OL-GDB6080	

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED