





1. MATERIAL:
BASE: UL94V-0 GLASS FILLED NYLON
STUDS: M5
2. TORQUE RATING: 5±1 Nm
3. FUSE RATING: 30-200A
4. WIRE SIZE: 14-4 AWG (2.5mm²-20mm²)
5. TEMPERATURE RATING: -40°C TO 125°C

PACKAGING NOTES:

1. PARTS ARE PACKED 50 PC PER BAG, 10 BAGS PER BOX.



INSERT MOLDED
M5 STUDS

METRIC

ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES												
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.												
◎ DENOTES CRITICAL CHARACTERISTICS.												
CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE												
ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS												
CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE												
BILL OF MATERIAL												
MATL SPEC												
FINISH												
SCALE 1:1												
SUPER DR												
FINSH GOOD WT GRAMS/PIECE												
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)												
DIMENSION 0.5 - 3 3 - 6 6 - 30 30 - 120 120 - 400												
TOLERANCE ±0.1 ±0.1 ±0.2 ±0.3 ±0.5												
3RD ANGLE PROJECTION												
TITLE BASE FOR MIDI INLINE HOLDER, W/M5 BOLTS												
REVISION A												
DRWG. NO. OL-498921-3												
OUTLINE												