





THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

PART NUMBER	DESCRIPTION
178.6165.0001	HOLDER - FLR (ATO) PCB 80V 4-PIN 100 PC
178.6165.0002	HOLDER - FLR (ATO) PCB 80V 4-PIN 500 PC

(H)



REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	C	IN CAD GEZ.	ULB	01/10/00
	D	AEND.Nr: 287	MAK	04/16/02
	E	AEND.Nr: 0058	HOEP	04/06/05
	F	AEND.Nr: 20113DN1	HOEP	06/03/06
	G	510213ECA-REDRAW IN UG	OPL	07/03/14
	H	ECN #523216: CLARIFY DIMENSIONS, ADD PN, UPDATE TEMPLATE	01/06/2021	S.CASTILLO

F

E

D

C

B

A

F

E

D

C

B

A

NOTES:
- MATERIAL:
** HOUSING: THERMOPLASTIC
** DFK1-TERMINALS F SOLDERING: Cu-ALLOY, Ag- PLATED

- GENERAL TOLERANCES: DIN 7168-m

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.			
		FIT FUNCTION CRITICAL CHARACTERISTICS SYMBOL	
<S>		SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL	
CPK		DENOTES CPK DIMENSIONS MINIMUM CPK VALUE	
		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS	
CP		DENOTES CP DIMENSIONS. MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE	
DIMENSION: MM TOLERANCES UNLESS OTHERWISE SPECIFIED ONE PLACE DECIMAL ± 0.5 THREE PLACES DECIMAL ± 0.100 TWO PLACES DECIMAL ± 0.20 ANGULAR ± 2°			
NAME		DATE	
DRAWN		03/14/14	
CHECKED		-	
-		-	
-		-	
-		-	
FORM NO: CVP-PE40-0006 REV A		THIRD ANGLE PROJECTION	
DO NOT SCALE DRAWING		SCALE 5:1	
SHEET 1 OF 1		SHEET 1 OF 1	
Littelfuse®		Expertise Applied Answers Delivered	
TITLE		HOLDER-FLR (ATO) PCV 80V 4-PIN	
SIZE	C	DWG. NO.	178.6165.0000
REV.	H		