





THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
REV.	CHANGE NO.	DESCRIPTION	DATE	APPROVED
A	520748	PRODUCTION RELEASE	05/29/2019	DGK
B	521389	ADDED TIN TO WIRE. ADDED HOLE DIMENSIONS.	10/16/2019	DGK



- NOTES:
1. HOUSING AND COVER MATERIAL: BLACK PC
 2. SEAL MATERIAL: SILICONE
 3. WIRE: 14 AWG STRANDED COPPER, RED GXL WIRE, 125°C TEMPERATURE RATING, TINNED
 4. FOR USE WITH ISO 8820 TYPE 'F' FUSE (MINI FUSE).
 5. RATING: 20A MAXIMUM, 32Vdc
 6. FUSEHOLDER IS DUST TIGHT AND PROTECTED AGAINST IMMERSION, IP67 RATED.
 7. FUSE IS NOT INCLUDED.
 8. FUSEHOLDER IS RoHS COMPLIANT.

INTERPRET DRAWING TO ANSI/ASME Y14.5-1994.				
	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL			
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL			
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE			
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
DIMENSION: MM TOLERANCES UNLESS OTHERWISE SPECIFIED ONE PLACE DECIMAL ± 0.5 THREE PLACES DECIMAL ± 0.100 TWO PLACES DECIMAL ± 0.20 ANGULAR ± 2°				
	NAME	DATE	 Expertise Applied Answers Delivered	
DRAWN	DGK	05/29/2019		
CHECKED	MS	06/26/2019		
	-	-		
	-	-	TITLE FUSEHOLDER, IN-LINE MINI 14 AWG GXL, SEALED	
FORM NO: CVP-PE40-0004 REV A			SIZE DWG. NO. REV. B OL-FHMS201 B	
THIRD ANGLE PROJECTION				
			SCALE 1:2 SHEET 1 OF 1	
DO NOT SCALE DRAWING				