





RECOMMENDED P.C.B. LAYOUT
(MOUNTING SIDE)

MATERIAL:
BODY-BLACK GLASS FILLED
THERMOPLASTIC (UL94V-0).
CLIP COPPER ALLOY, TIN PLATE FINISH

TOLERANCES:
TWO PLACE DEC ±.01
THREE PLACE DEC ±.005

METRIC
ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES.									
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.									
◀▶	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE.								
●	CRITICAL CHARACTERISTIC FOR PART FIT/FUNCTION.								
CPK	CPK DIMENSION. 1.67 MINIMUM CPK VALUE ON NEW TOOLING.								
ST	STATISTICAL PROCESS CONTROL DIMENSION. THIS DIMENSION INDICATES PROCESS PERFORMANCE. DATA SHALL BE TRACKED AND ANALYZED AT PERIODIC TIMES, ACC. TO CONTROL PLAN.								
CP	CP DIMENSION. 1.67 MINIMUM CP VALUE. MUST BE INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.								
Q	CUSTOMER-DESIGNATED CHARACTERISTIC. REQUIREMENT FOR EACH SYMBOL TO BE DEFINED IN A CONVERSION TABLE.								
△	CLAMP DIMENSION. PARTS SHALL BE SECURED BEFORE TAKING DIMENSIONAL MEASUREMENTS. FIXTURING DATUMS & PROCEDURES TO BE DEFINED IN NOTES OR SEPARATE PROCESS DOCUMENTS.								

DIMENSIONS & TOLERANCES ACC. TO ASME Y14.5-2009													MATL SPEC -													SIZE B																									
3RD ANGLE PROJECTION 													FINISH -																																						
SCALE -													DRW OPL													CHK MZAM													DATE 12 / JAN / 18												
TOLERANCES UNLESS OTHERWISE SPECIFIED																																																			
LINEAR DIMENSIONS																																																			
DIM										UP TO .5		OVER 6		UP TO 30		OVER 30		UP TO 120		OVER 120		UP TO 400		ANGLES										RADI																	
TOL										±0.1		±0.2		±0.3		±0.5		±0.5		±0.5		±0.5°										±0.2																			
TITLE MINIFUSE SINGLE VERTICAL MOUNT P.C.B. HOLDER																																																			
REVISION													DRAWG. NO.																																						
A													OL-01530032Z																																						