





VERSIONS AND PART NUMBERS					
CURREN RATE [A]	M6 1 HOLE	M6 2 HOLES	M8 1 HOLE	M8 2 HOLES	NO HOLES
60	0998060.U-1M6	0998060.U-2M6	0998060.U-1M8	0998060.U-2M8	0998060.U-NH
80	0998080.U-1M6	0998080.U-2M6	0998080.U-1M8	0998080.U-2M8	0998080.U-NH
100	0998100.U-1M6	0998100.U-2M6	0998100.U-1M8	0998100.U-2M8	0998100.U-NH
125	0998125.U-1M6	0998125.U-2M6	0998125.U-1M8	0998125.U-2M8	0998125.U-NH
150	0998150.U-1M6	0998150.U-2M6	0998150.U-1M8	0998150.U-2M8	0998150.U-NH
175	0998175.U-1M6	0998175.U-2M6	0998175.U-1M8	0998175.U-2M8	0998175.U-NH
200	0998200.U-1M6	0998200.U-2M6	0998200.U-1M8	0998200.U-2M8	0998200.U-NH
225	0998225.U-1M6	0998225.U-2M6	0998225.U-1M8	0998225.U-2M8	0998225.U-NH
250	0998250.U-1M6	0998250.U-2M6	0998250.U-1M8	0998250.U-2M8	0998250.U-NH
300	0998300.U-1M6	0998300.U-2M6	0998300.U-1M8	0998300.U-2M8	0998300.U-NH
350	0998350.U-1M6	0998350.U-2M6	0998350.U-1M8	0998350.U-2M8	0998350.U-NH
400	0998400.U-1M6	0998400.U-2M6	0998400.U-1M8	0998400.U-2M8	0998400.U-NH
450	0998450.U-1M6	0998450.U-2M6	0998450.U-1M8	0998450.U-2M8	0998450.U-NH
500	0998500.U-1M6	0998500.U-2M6	0998500.U-1M8	0998500.U-2M8	0998500.U-NH


LTR	DATE	REVISION	DRW
A	01/FEB/23	526136GCA - INITIAL RELEASE	OPL




ISOMETRIC VIEW




0998XXX.U-1M8



0998XXX.U-2M6



0998XXX.U-1M6



0998XXX.U-NH

MEGA HP 70V (SF51)					
TERMINAL MATERIAL :		COPPER			
TERMINAL PLATING :		TIN			
HOUSING MATERIAL :		PPA-GF33 (U.L. 94 FLAMMABILITY RATING - HB)			
LINEAR DIMENSIONS					ANGLES
DIM	.5 - 6	6 - 30	30 - 120	120 - 400	±0.5°
TOL	±0.1	±0.2	±0.3	±0.5	
REVISION					DRWG. NO.
A					WEB-0998000.U

