


Ø63.5 ± 0.38
[Ø2.50 ± 0.015]

9.5 ± 0.08
[0.38 ± 0.003]



50.8 ± 0.89
[2.00 ± 0.035]

13.5 ± 0.13
[0.53 ± 0.005]

203.2 ± 2.29
[8.00 ± 0.090]

152.0 ± 1.52
[5.98 ± 0.060]

95.3 ± 0.76
[3.75 ± 0.030]

17.9 ^{+1.57}_{-0.00}
[0.70 ^{+0.062}_{-0.000}]

REVISION				
REV	DATE	DESCRIPTION		
A	10/14/22	525789GCP - RELEASE MRY		

1	NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE				
●	DENOTES CRITICAL CHARACTERISTICS.				
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE				
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.				
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.				
MATL SPEC			FINISH		
DRW	JMOLER	DATE	10/13/2022	SCALE	NTS
				FINISH GOOD WT	GRAMS/PIECE
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994					
3RD ANGLE PROJECTION					
TITLE SPFJ 450A OUTLINE					
 Littelfuse CHICAGO, ILLINOIS 60631			REVISION	DRWG NO.	SHEET 1 OF 1
			A	OL-SPFJ450	