

SMF3.3

Surface Mount – 200W



Additional Information



Resources



Accessories



Samples

Agency Approvals

Agency	Agency File Number
	E230531

Maximum Ratings and Thermal Characteristics

(T_A = 25 °C unless otherwise noted)

Parameter	Symbol	Value	Unit
Peak Pulse Power Dissipation at T _A = 25°C (Note 1)	P _{PPM}	1200	W
8/20µs (Note 2)		200	W
10/1000µs (Note 3)			
Thermal Resistance Junction- to- Ambient	R _{θJA}	220	°C/W
Thermal Resistance Junction- to- Lead	R _{θJL}	100	°C/W
Operating Temperature Range	T _J	-55 to 150	°C
Storage Temperature Range	T _{STG}	-55 to 150	°C

Notes:

1. Non-repetitive current pulse, per Fig. 4 and derated above T_J (initial) = 25°C per Fig. 3.

Description

SMF3.3 is designed specifically to protect sensitive electronic equipment from voltage transients induced by lightning and other transient voltage events.


Features and Benefits

- 200W peak pulse power capability at 10/1000µs waveform, repetition rate (duty cycle): 0.01 %
- 1200W peak pulse power capability at 8/20µs waveform
- Excellent clamping capability
- Compatible with industrial standard package SOD-123FL
- Low profile: maximum height of 1.08mm.
- For surface mounted applications to optimize board space
- Typical failure mode is short from over-specified voltage or current
- Whisker test is conducted based on JEDEC JESD201A per its table 4a and 4c
- IEC 61000-4-2 ESD 30kV(Air), 30kV (Contact)
- ESD protection of data lines in accordance with IEC 61000-4-2
- EFT protection of data lines in accordance with IEC 61000-4-4
- Fast response time: typically less than 1.0ns from 0 Volts to VBR min
- High temperature soldering: 260°C/30 seconds at terminals
- Built-in strain relief
- Meet MSL level1, per J-STD-020C, LF maximum peak of 260°C
- Matte tin lead-free plated
- Halogen-free and RoHS-compliant
- Pb-free E3 means 2nd level interconnect is Pb-free and the terminal finish material is tin(Sn) (IPC/JEDEC J-STD-609A.01)

Applications

SMF3.3 series is ideal for the protection of portable electronics/ hard drives, notebooks, VCC busses, POS terminal, SSDs, power supplies, monitors, and vulnerable circuit used in other consumer applications.

Functional Diagram

Electrical Characteristics (T_A = 25°C unless otherwise noted)






Part Number	Marking Code	Breakdown Voltage V _{BR} (Volts) @ I _T		Test Current I _T (mA)	Reverse Stand off Voltage V _R (V)	Maximum Reverse Leakage @ V _R I _R (µA)	Maximum Peak Pulse Current (10/1000µS) I _{PP} (A)	Maximum Clamping Voltage @ I _{PP} (10/1000µS) V _C (V)	Maximum Peak Pulse Current (8/20µS) I _{PP} (A)	Maximum Clamping Voltage @ I _{PP} (8/20µS) V _C (V)
		MIN	MAX							
SMF3.3	33	3.4	4.3	10	3.3	0.5	30.0	6.8	120.0	10.0

Notes:

1. V_{BR} measured after I_T applied for 300µs, I_T = square wave pulse or equivalent.
2. Surge current waveform per 10/1000µs exponential wave and derated per Fig.2.
3. All terms and symbols are consistent with ANSI/IEEE C62.35.
4. Surge current waveform per 8/20µs exponential wave and derated per Fig.6.

SMF3.3

Surface Mount – 200W

I-V Curve Characteristics **P_{PPM} Peak Pulse Power Dissipation** – Max power dissipation **V_R Stand-off Voltage** -- Maximum voltage that can be applied to the TVS without operation **V_{BR} Breakdown Voltage** -- Maximum voltage that flows through the TVS at a specified test current (I_T) **V_C Clamping Voltage** -- Peak voltage measured across the TVS at a specified I_{PPM} (peak impulse current) **I_R Reverse Leakage Current** – Current measured at V_R **V_F Forward Voltage Drop for Uni-directional****Note:** V_F distribution range from 7V to 16V at I_F 1mA.**Ratings and Characteristic Curves** ($T_A=25^\circ\text{C}$ unless otherwise noted)**Figure 1 -**
TVS Transients Clamping Waveform**Figure 2 -**
Peak Pulse Power Rating Curve**Figure 3 -**
Peak Pulse Power Derating Curve**Figure 4 -**
10/1000 μs Pulse Waveform

SMF3.3

Surface Mount – 200W

Figure 5 -
Capacitance vs. Reverse Bias






Figure 6 -
8/20μS Pulse Waveform



Soldering Parameters

Reflow Condition		Lead-free assembly
Pre Heat	- Temperature Min ($T_{s(min)}$)	150°C
	- Temperature Max ($T_{s(max)}$)	200°C
	- Time (min to max) (t_s)	60 – 120 secs
Average ramp up rate (Liquidus Temp (T_L) to peak)		3°C/second max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/second max
Reflow	- Temperature (T_L) (Liquidus)	217°C
	- Time (min to max) (t_L)	60 – 150 seconds
Peak Temperature (T_p)		260 ^{+0/-5} °C
Time within 5°C of actual peak Temperature (t_p)		30 seconds max
Ramp-down Rate		6°C/second max
Time 25°C to peak Temperature (T_p)		8 minutes max.
Do not exceed		260°C



Physical Specifications

Case	SOD-123FL plastic over passivated junction
Polarity	Color band denotes cathode except bipolar
Terminal	Matte tin-plated leads, solderable per JESD22-B102


Environmental Specification

High Temp. Storage	JESD22-A103
HTRB	JESD22-A108
Temperature Cycling	JESD22-A104
MSL	JEDEC-J-STD-020, LEVEL 1
H3TRB	JESD22-A101
RSH	JESD22-A111

SMF3.3


Surface Mount – 200W

Dimensions - SOD-123FL Package




Dimensions	Millimeters		Inches	
	Min	Max	Min	Max
A	2.70	3.10	0.106	0.122
B	3.50	3.90	0.138	0.154
C	0.85	1.05	0.033	0.041
D	1.70	2.00	0.067	0.079
E	0.43	0.83	0.017	0.033
F	0.10	0.25	0.004	0.010
G	0.00	0.10	0.000	0.004
H	0.90	1.08	0.035	0.043
I	0.00	0.20	0.000	0.008
J	0.40	0.60	0.016	0.024

Part Numbering System





Part Marking System



Packaging Options

Part number	Component Package	Quantity	Packaging Option	Packaging Specification
SMF3.3	SOD-123FL	3000	Tape & Reel – 8mm tape/7" reel	EIA RS-481

Tape and Reel Specification



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.