


# PolarHV™ HiPerFET Power MOSFET

N-Channel Enhancement Mode  
Avalanche Rated  
Fast Intrinsic Diode

IXFH 14N80P  
IXFQ 14N80P  
IXFT 14N80P  
IXFV 14N80P  
IXFV 14N80PS




| Symbol     | Test Conditions                                                                                                                         | Maximum Ratings |                  |
|------------|-----------------------------------------------------------------------------------------------------------------------------------------|-----------------|------------------|
| $V_{DSS}$  | $T_J = 25^\circ\text{C}$ to $175^\circ\text{C}$                                                                                         | 800             | V                |
| $V_{DGR}$  | $T_J = 25^\circ\text{C}$ to $175^\circ\text{C}$ ; $R_{GS} = 1\text{ M}\Omega$                                                           | 800             | V                |
| $V_{GS}$   | Continuous                                                                                                                              | $\pm 30$        | V                |
| $V_{GSM}$  | Transient                                                                                                                               | $\pm 40$        | V                |
| $I_{D25}$  | $T_C = 25^\circ\text{C}$                                                                                                                | 14              | A                |
| $I_{DM}$   | $T_C = 25^\circ\text{C}$ , pulse width limited by $T_{JM}$                                                                              | 40              | A                |
| $I_{AR}$   | $T_C = 25^\circ\text{C}$                                                                                                                | 7               | A                |
| $E_{AR}$   | $T_C = 25^\circ\text{C}$                                                                                                                | 30              | mJ               |
| $E_{AS}$   | $T_C = 25^\circ\text{C}$                                                                                                                | 500             | mJ               |
| $dv/dt$    | $I_S \leq I_{DM}$ , $di/dt \leq 100\text{ A}/\mu\text{s}$ , $V_{DD} \leq V_{DSS}$ ,<br>$T_J \leq 150^\circ\text{C}$ , $R_G = 5\ \Omega$ | 10              | V/ns             |
| $P_D$      | $T_C = 25^\circ\text{C}$                                                                                                                | 400             | W                |
| $T_J$      |                                                                                                                                         | -55 ... +150    | $^\circ\text{C}$ |
| $T_{JM}$   |                                                                                                                                         | 150             | $^\circ\text{C}$ |
| $T_{stg}$  |                                                                                                                                         | -55 ... +150    | $^\circ\text{C}$ |
| $T_L$      | 1.6 mm (0.062 in.) from case for 10 s                                                                                                   | 300             | $^\circ\text{C}$ |
| $T_{SOLD}$ | Plastic body for 10 s                                                                                                                   | 260             | $^\circ\text{C}$ |
| $M_d$      | Mounting torque (TO-247, TO-3P)                                                                                                         | 1.13/10         | Nm/lb.in.        |
| Weight     | PLUS220, PLUS220 SMD                                                                                                                    | 2               | g                |
|            | TO-268, TO-3P                                                                                                                           | 5.5             | g                |
|            | TO-247                                                                                                                                  | 6               | g                |


| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified)                                     | Characteristic Values |      |                          |
|--------------|-----------------------------------------------------------------------------------------------------------------|-----------------------|------|--------------------------|
|              |                                                                                                                 | Min.                  | Typ. | Max.                     |
| $BV_{DSS}$   | $V_{GS} = 0\text{ V}$ , $I_D = 250\mu\text{A}$                                                                  | 800                   |      | V                        |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 4\text{ mA}$                                                                         | 3.0                   |      | 5.5 V                    |
| $I_{GSS}$    | $V_{GS} = \pm 30\text{ V}$ , $V_{DS} = 0\text{ V}$                                                              |                       |      | $\pm 100\text{ nA}$      |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$<br>$V_{GS} = 0\text{ V}$<br>$T_J = 125^\circ\text{C}$                                        |                       |      | 25 $\mu\text{A}$<br>1 mA |
| $R_{DS(on)}$ | $V_{GS} = 10\text{ V}$ , $I_D = 0.5 I_{D25}$<br>Pulse test, $t \leq 300\ \mu\text{s}$ , duty cycle $d \leq 2\%$ |                       |      | 720 m $\Omega$           |

$V_{DSS} = 800\text{ V}$   
 $I_{D25} = 14\text{ A}$   
 $R_{DS(on)} \leq 720\text{ m}\Omega$   
 $t_{rr} \leq 250\text{ ms}$


TO-247 (IXFH)




TO-3P (IXFQ)




TO-268 (IXFT)



PLUS220 (IXFV)



PLUS220SMD (IXFV...S)



G = Gate  
S = Source  
D = Drain  
TAB = Drain

## Features

- International standard packages
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
  - easy to drive and to protect


## Advantages

- Easy to mount
- Space savings
- High power density

| Symbol       | Test Conditions                                                                                   | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |                          |
|--------------|---------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|--------------------------|
|              |                                                                                                   | Min.                                                                              | Typ. | Max.                     |
| $g_{fs}$     | $V_{DS} = 20\text{ V}$ ; $I_D = 0.5 I_{D25}$ , pulse test                                         | 8                                                                                 | 15   | S                        |
| $C_{iss}$    | $V_{GS} = 0\text{ V}$ , $V_{DS} = 25\text{ V}$ , $f = 1\text{ MHz}$                               |                                                                                   | 3900 | pF                       |
| $C_{oss}$    |                                                                                                   |                                                                                   | 250  | pF                       |
| $C_{rss}$    |                                                                                                   |                                                                                   | 19   | pF                       |
| $t_{d(on)}$  | $V_{GS} = 10\text{ V}$ , $V_{DS} = 0.5 V_{DSS}$ , $I_D = I_{D25}$<br>$R_G = 5\ \Omega$ (External) |                                                                                   | 26   | ns                       |
| $t_r$        |                                                                                                   |                                                                                   | 29   | ns                       |
| $t_{d(off)}$ |                                                                                                   |                                                                                   | 62   | ns                       |
| $t_f$        |                                                                                                   |                                                                                   | 27   | ns                       |
| $Q_{g(on)}$  | $V_{GS} = 10\text{ V}$ , $V_{DS} = 0.5 V_{DSS}$ , $I_D = 0.5 I_{D25}$                             |                                                                                   | 61   | nC                       |
| $Q_{gs}$     |                                                                                                   |                                                                                   | 18   | nC                       |
| $Q_{gd}$     |                                                                                                   |                                                                                   | 20   | nC                       |
| $R_{thJC}$   | (TO-247, TO-3P)                                                                                   |                                                                                   | 0.21 | $0.31\ ^\circ\text{C/W}$ |
| $R_{thCS}$   |                                                                                                   |                                                                                   |      | $^\circ\text{C/W}$       |

| Symbol   | Test Conditions                                                                                          | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |               |
|----------|----------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|---------------|
|          |                                                                                                          | Min.                                                                              | Typ. | Max.          |
| $I_s$    | $V_{GS} = 0\text{ V}$                                                                                    |                                                                                   |      | 14 A          |
| $I_{SM}$ | Repetitive                                                                                               |                                                                                   |      | 40 A          |
| $V_{SD}$ | $I_F = I_s$ , $V_{GS} = 0\text{ V}$ ,<br>Pulse test, $t \leq 300\ \mu\text{s}$ , duty cycle $d \leq 2\%$ |                                                                                   |      | 1.5 V         |
| $t_{rr}$ | $I_F = 25\text{ A}$ ,<br>-di/dt = 100 A/ $\mu\text{s}$<br>$V_R = 100\text{ V}$                           |                                                                                   | 0.4  | 250 ns        |
| $Q_{RM}$ |                                                                                                          |                                                                                   |      | $\mu\text{C}$ |
| $I_{RM}$ |                                                                                                          |                                                                                   |      | A             |


### PLUS220SMD (IXFV\_S) Outline



| SYM | INCHES   |      | MILLIMETER |       |
|-----|----------|------|------------|-------|
|     | MIN      | MAX  | MIN        | MAX   |
| A   | .169     | .185 | 4.30       | 4.70  |
| A1  | .028     | .035 | 0.70       | 0.90  |
| A2  | .098     | .118 | 2.50       | 3.00  |
| A3  | .000     | .010 | 0.00       | 0.25  |
| b   | .035     | .047 | 0.90       | 1.20  |
| b1  | .080     | .095 | 2.03       | 2.41  |
| b2  | .054     | .064 | 1.37       | 1.63  |
| c   | .028     | .035 | 0.70       | 0.90  |
| D   | .551     | .591 | 14.00      | 15.00 |
| D1  | .512     | .539 | 13.00      | 13.70 |
| E   | .394     | .433 | 10.00      | 11.00 |
| E1  | .331     | .346 | 8.40       | 8.80  |
| e   | .200 BSC |      | 5.08 BSC   |       |
| L   | .209     | .228 | 5.30       | 5.80  |
| L1  | .118     | .138 | 3.00       | 3.50  |
| L2  | .035     | .051 | 0.90       | 1.30  |
| L3  | .047     | .059 | 1.20       | 1.50  |
| L4  | .039     | .059 | 1.00       | 1.50  |

1. GATE
2. DRAIN (COLLECTOR)
3. SOURCE (EMITTER)
4. DRAIN (COLLECTOR)



### TO-247 (IXFH) Outline



Terminals: 1 - Gate  
2 - Drain  
3 - Source  
Tab - Drain

| Dim. | Millimeter |       | Inches |       |
|------|------------|-------|--------|-------|
|      | Min.       | Max.  | Min.   | Max.  |
| A    | 4.7        | 5.3   | .185   | .209  |
| A1   | 2.2        | 2.54  | .087   | .102  |
| A2   | 2.2        | 2.6   | .059   | .098  |
| b    | 1.0        | 1.4   | .040   | .055  |
| b1   | 1.65       | 2.13  | .065   | .084  |
| b2   | 2.87       | 3.12  | .113   | .123  |
| C    | .4         | .8    | .016   | .031  |
| D    | 20.80      | 21.46 | .819   | .845  |
| E    | 15.75      | 16.26 | .610   | .640  |
| e    | 5.20       | 5.72  | 0.205  | 0.225 |
| L    | 19.81      | 20.32 | .780   | .800  |
| L1   |            | 4.50  |        | .177  |
| ØP   | 3.55       | 3.65  | .140   | .144  |
| Q    | 5.89       | 6.40  | 0.232  | 0.252 |
| R    | 4.32       | 5.49  | .170   | .216  |
| S    | 6.15       | BSC   | 242    | BSC   |

### TO-268 (IXFT) Outline




| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .193     | .201 | 4.90        | 5.10  |
| A1  | .106     | .114 | 2.70        | 2.90  |
| A2  | .001     | .010 | 0.02        | 0.25  |
| b   | .045     | .057 | 1.15        | 1.45  |
| b2  | .075     | .083 | 1.90        | 2.10  |
| C   | .016     | .026 | 0.40        | 0.65  |
| C2  | .057     | .063 | 1.45        | 1.60  |
| D   | .543     | .551 | 13.80       | 14.00 |
| D1  | .488     | .500 | 12.40       | 12.70 |
| E   | .624     | .632 | 15.85       | 16.05 |
| E1  | .524     | .535 | 13.30       | 13.60 |
| e   | .215 BSC |      | 5.45 BSC    |       |
| H   | .736     | .752 | 18.70       | 19.10 |
| L   | .094     | .106 | 2.40        | 2.70  |
| L1  | .047     | .055 | 1.20        | 1.40  |
| L2  | .039     | .045 | 1.00        | 1.15  |
| L3  | .010     | BSC  | 0.25        | BSC   |
| L4  | .150     | .161 | 3.80        | 4.10  |


IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by 4,835,592 4,931,844 5,049,961 5,237,481 6,162,665 6,404,065 B1 6,683,344 6,727,585 7,005,734 B2  
one or more of the following U.S. patents: 4,850,072 5,017,508 5,063,307 5,381,025 6,259,123 B1 6,534,343 6,710,405 B2 6,759,692 7,063,975 B2  
4,881,106 5,034,796 5,187,117 5,486,715 6,306,728 B1 6,583,505 6,710,463 6,771,478 B2 7,071,537


**Fig. 1. Output Characteristics  
@ 25°C**




**Fig. 2. Extended Output Characteristics  
@ 25°C**




**Fig. 3. Output Characteristics  
@ 125°C**



**Fig. 4.  $R_{DS(on)}$  Normalized to  $I_D = 7A$  Value vs.  
Junction Temperature**



**Fig. 5.  $R_{DS(on)}$  Normalized to  $I_D = 7A$  Value vs.  
Drain Current**



**Fig. 6. Maximum Drain Current vs.  
Case Temperature**




Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance






Fig. 13. Maximum Transient Thermal Resistance



### TO-3P-3L PACKAGE Outline




ALL METAL AREA ARE TIN PLATED.

| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .185     | .193 | 4.70        | 4.90  |
| A1  | .051     | .059 | 1.30        | 1.50  |
| A2  | .057     | .065 | 1.45        | 1.65  |
| b   | .035     | .045 | 0.90        | 1.15  |
| b2  | .075     | .087 | 1.90        | 2.20  |
| b4  | .114     | .126 | 2.90        | 3.20  |
| c   | .022     | .031 | 0.55        | 0.80  |
| D   | .780     | .799 | 19.80       | 20.30 |
| D1  | .665     | .677 | 16.90       | 17.20 |
| E   | .610     | .622 | 15.50       | 15.80 |
| E1  | .531     | .539 | 13.50       | 13.70 |
| e   | .215 BSC |      | 5.45 BSC    |       |
| L   | .779     | .795 | 19.80       | 20.20 |
| L1  | .134     | .142 | 3.40        | 3.60  |
| øP  | .126     | .134 | 3.20        | 3.40  |
| øP1 | .272     | .280 | 6.90        | 7.10  |
| S   | .193     | .201 | 4.90        | 5.10  |

Ref: IXYS CO 0170 RA

### PLUS220 (IXFV) Outline



| SYM | INCHES   |      | MILLIMETER |       |
|-----|----------|------|------------|-------|
|     | MIN      | MAX  | MIN        | MAX   |
| A   | .169     | .185 | 4.30       | 4.70  |
| A1  | .028     | .035 | 0.70       | 0.90  |
| A2  | .098     | .118 | 2.50       | 3.00  |
| b   | .035     | .047 | 0.90       | 1.20  |
| b1  | .080     | .095 | 2.03       | 2.41  |
| b2  | .054     | .064 | 1.37       | 1.63  |
| c   | .028     | .035 | 0.70       | 0.90  |
| D   | .551     | .591 | 14.00      | 15.00 |
| D1  | .512     | .539 | 13.00      | 13.70 |
| E   | .394     | .433 | 10.00      | 11.00 |
| E1  | .331     | .346 | 8.40       | 8.80  |
| e   | .100 BSC |      | 2.54 BSC   |       |
| L   | .512     | .551 | 13.00      | 14.00 |
| L1  | .118     | .138 | 3.00       | 3.50  |
| L2  | .035     | .051 | 0.90       | 1.30  |
| L3  | .047     | .059 | 1.20       | 1.50  |



---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).