

preliminary


Schottky Diode Gen ²

$$\begin{aligned}
 V_{RRM} &= 60 \text{ V} \\
 I_{FAV} &= 2 \times 30 \text{ A} \\
 V_F &= 0.75 \text{ V}
 \end{aligned}$$


High Performance Schottky Diode
 Low Loss and Soft Recovery
 Common Cathode

Part number

DSA60C60HB



Backside: cathode



Features / Advantages:

- Very low V_f
- Extremely low switching losses
- Low I_{rm} values
- Improved thermal behaviour
- High reliability circuit operation
- Low voltage peaks for reduced protection circuits
- Low noise switching

Applications:

- Rectifiers in switch mode power supplies (SMPS)
- Free wheeling diode in low voltage converters

Package: TO-247

- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0

Disclaimer Notice


Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

Schottky				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
V _{RSM}	max. non-repetitive reverse blocking voltage	T _{VJ} = 25°C				60	V
V _{RRM}	max. repetitive reverse blocking voltage	T _{VJ} = 25°C				60	V
I _R	reverse current, drain current	V _R = 60 V	T _{VJ} = 25°C			450	μA
		V _R = 60 V	T _{VJ} = 125°C			5	mA
V _F	forward voltage drop	I _F = 30 A	T _{VJ} = 25°C			0.91	V
		I _F = 60 A				1.14	V
		I _F = 30 A	T _{VJ} = 125°C			0.75	V
		I _F = 60 A				0.96	V
I _{FAV}	average forward current	T _C = 150°C rectangular d = 0.5	T _{VJ} = 175°C			30	A
V _{F0}	threshold voltage	} for power loss calculation only				0.49	V
r _F	slope resistance					6.2	mΩ
R _{thJC}	thermal resistance junction to case					0.95	K/W
R _{thCH}	thermal resistance case to heatsink				0.3		K/W
P _{tot}	total power dissipation	T _C = 25°C				160	W
I _{FSM}	max. forward surge current	t = 10 ms; (50 Hz), sine; V _R = 0 V				550	A
C _J	junction capacitance	V _R = 12 V f = 1 MHz			449		pF

preliminary

Package TO-247			Ratings			
Symbol	Definition	Conditions	min.	typ.	max.	Unit
I_{RMS}	RMS current	per terminal ¹⁾			50	A
T_{VJ}	virtual junction temperature		-55		175	°C
T_{op}	operation temperature		-55		150	°C
T_{stg}	storage temperature		-55		150	°C
Weight				6		g
M_D	mounting torque		0.8		1.2	Nm
F_C	mounting force with clip		20		120	N

Product Marking



Part description

D = Diode
 S = Schottky Diode
 A = low VF
 60 = Current Rating [A]
 C = Common Cathode
 60 = Reverse Voltage [V]
 HB = TO-247AD (3)


Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	DSA60C60HB	DSA60C60HB	Tube	30	506722


Similar Part	Package	Voltage class
DSA60C60PB	TO-220AB (3)	60

Equivalent Circuits for Simulation

* on die level

 $T_{VJ} = 175^{\circ}\text{C}$

		Schottky	
$V_{0\max}$	threshold voltage	0.49	V
$R_{0\max}$	slope resistance *	3.6	mΩ

Outlines TO-247


Sym.	Inches		Millimeter	
	min.	max.	min.	max.
A	0.185	0.209	4.70	5.30
A1	0.087	0.102	2.21	2.59
A2	0.059	0.098	1.50	2.49
D	0.819	0.845	20.79	21.45
E	0.610	0.640	15.48	16.24
E2	0.170	0.216	4.31	5.48
e	0.215	BSC	5.46	BSC
L	0.780	0.800	19.80	20.30
L1	-	0.177	-	4.49
Ø P	0.140	0.144	3.55	3.65
Q	0.212	0.244	5.38	6.19
S	0.242	BSC	6.14	BSC
b	0.039	0.055	0.99	1.40
b2	0.065	0.094	1.65	2.39
b4	0.102	0.135	2.59	3.43
c	0.015	0.035	0.38	0.89
D1	0.515	-	13.07	-
D2	0.020	0.053	0.51	1.35
E1	0.530	-	13.45	-
Ø P1	-	0.29	-	7.39

