



SRDA3.3 Series 8pF 35A Diode Array




Pinout



SOIC-8 (Top View)

Note: Pinout diagrams above shown as device footprint on circuit board.

Functional Block Diagram



Life Support Note:

Not Intended for Use in Life Support or Life Saving Applications

The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

Description

The SRDA3.3 integrates low capacitance rail-to-rail diodes with an additional zener diode to protect I/O pins against ESD and lightning induced surge events. This device can safely absorb up to 35A per IEC61000-4-5 ($t_p=8/20\mu s$) without performance degradation and a minimum $\pm 30kV$ ESD per IEC61000-4-2 international standard. Its low loading capacitance makes it ideal for high-speed interface protection.


Features

- Lightning protection, IEC61000-4-5, 35A (8/20 μs)
- EFT, IEC61000-4-4, 50A (5/50ns)
- ESD, IEC61000-4-2, $\pm 30kV$ contact, $\pm 30kV$ air
- Low clamping voltage
- Low leakage current
- SOIC-8 surface mount package (JEDEC MS-012)

Applications

- Tertiary (IC Side) Protection:
 - T1/E1/T3/E3
 - HDSL/SDSL
 - Ethernet
- RS232, RS485
- Video Line Protection
- Security Cameras
- Storage DVRs
- Network Equipment
- Instrumentation, Medical Equipment

Application Example



T1/E1/T3/E3 Interface Protection

Absolute Maximum Ratings

| Symbol | Parameter | Value | Units |
|------------|-----------------------------------|------------|-------|
| P_{pk} | Peak Pulse Power (8/20 μ s) | 600 | W |
| I_{pp} | Peak Pulse Current (8/20 μ s) | 35 | A |
| T_{op} | Operating Temperature | -40 to 125 | °C |
| T_{stor} | Storage Temperature | -55 to 150 | °C |

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

Thermal Information


| Parameter | Rating | Units |
|---|------------|-------|
| SOIC Package | 170 | °C/W |
| Operating Temperature Range | -40 to 125 | °C |
| Storage Temperature Range | -55 to 150 | °C |
| Maximum Junction Temperature | 150 | °C |
| Maximum Lead Temperature (Soldering 20-40s) (SOIC - Lead Tips Only) | 260 | °C |

Electrical Characteristics ($T_{op} = 25^{\circ}\text{C}$)


| Parameter | Symbol | Test Conditions | Min | Typ | Max | Units |
|--|---------------|---|----------|------|-----|---------------|
| Reverse Stand-Off Voltage | V_{RWM} | $I_T \leq 1\mu\text{A}$ | - | - | 3.3 | V |
| Reverse Breakdown Voltage | V_{BR} | $I_T = 2\mu\text{A}$ | 3.5 | - | - | V |
| Snap Back Voltage | V_{SB} | $I_T = 50\text{mA}$ | 2.9 | - | - | V |
| Reverse Leakage Current | I_R | $V_R = 3.3\text{V}$ | - | - | 1 | μA |
| Clamping Voltage, Line-Ground ¹ | V_C | $I_{pp} = 1\text{A}, t_p = 8/20 \mu\text{s}$ | - | 5.7 | - | V |
| Clamping Voltage, Line-Ground ¹ | V_C | $I_{pp} = 10\text{A}, t_p = 8/20 \mu\text{s}$ | - | 10.1 | - | V |
| Clamping Voltage, Line-Ground ¹ | V_C | $I_{pp} = 30\text{A}, t_p = 8/20 \mu\text{s}$ | - | 17.7 | - | V |
| Dynamic Resistance, Line-Ground ¹ | R_{DYN} | $(V_{C2} - V_{C1}) / (I_{PP2} - I_{PP1})$ | - | 0.5 | - | Ω |
| ESD Withstand Voltage ¹ | V_{ESD} | IEC61000-4-2 (Contact Discharge) | ± 30 | - | - | kV |
| | | IEC61000-4-2 (Air Discharge) | ± 30 | - | - | kV |
| Diode Capacitance ¹ | $C_{I/O-I/O}$ | Reverse Bias=0V | - | 4.0 | - | pF |
| | $C_{I/O-GND}$ | Reverse Bias=0V | - | 8.0 | - | pF |

¹ Parameter is guaranteed by design and/or device characterization.


Normalized Capacitance vs. Bias Voltage




Non-Repetitive Peak Pulse Power vs. Pulse Time




Clamping Voltage vs. I_{PP}



Power Derating Curve



Pulse Waveform



Product Characteristics


| | |
|----------------------------|-------------------------|
| Lead Plating | Matte Tin |
| Lead Material | Copper Alloy |
| Lead Coplanarity | 0.0004 inches (0.102mm) |
| Substitute Material | Silicon |
| Body Material | Molded Epoxy |
| Flammability | UL 94 V-0 |

Notes :


- All dimensions are in millimeters
- Dimensions include solder plating.
- Dimensions are exclusive of mold flash & metal burr.
- Blo is facing up for mold and facing down for trim/form, i.e. reverse trim/form.
- Package surface matte finish VDI 11-13.

Soldering Parameters


| | | |
|--|------------------------------------|-------------------------|
| Reflow Condition | | Pb – Free assembly |
| Pre Heat | - Temperature Min ($T_{s(min)}$) | 150°C |
| | - Temperature Max ($T_{s(max)}$) | 200°C |
| | - Time (min to max) (t_s) | 60 – 180 secs |
| Average ramp up rate (Liquidus Temp (T_L) to peak) | | 3°C/second max |
| $T_{s(max)}$ to T_L - Ramp-up Rate | | 3°C/second max |
| Reflow | - Temperature (T_L) (Liquidus) | 217°C |
| | - Temperature (t_L) | 60 – 150 seconds |
| Peak Temperature (T_p) | | 260 ^{+0/-5} °C |
| Time within 5°C of actual peak Temperature (t_p) | | 20 – 40 seconds |
| Ramp-down Rate | | 6°C/second max |
| Time 25°C to peak Temperature (T_p) | | 8 minutes Max. |
| Do not exceed | | 260°C |



Part Numbering System




Part Marking System



Ordering Information


| Part Number | Package | Marking | Min. Order Qty. |
|--------------|---------|---------|-----------------|
| SRDA3.3-4BTG | SOIC-8 | SRDA3.3 | 2500 |

Package Dimensions – Mechanical Drawings and Recommended Solder Pad Outline



| Package | SOIC | | | |
|-----------|-------------|------|-----------|-------|
| Pins | 8 | | | |
| JEDEC | MS-012 | | | |
| | Millimetres | | Inches | |
| | Min | Max | Min | Max |
| A | 1.35 | 1.75 | 0.053 | 0.069 |
| A1 | 0.10 | 0.25 | 0.004 | 0.010 |
| A2 | 1.25 | 1.65 | 0.050 | 0.065 |
| B | 0.31 | 0.51 | 0.012 | 0.020 |
| c | 0.17 | 0.25 | 0.007 | 0.010 |
| D | 4.80 | 5.00 | 0.189 | 0.197 |
| E | 5.80 | 6.20 | 0.228 | 0.244 |
| E1 | 3.80 | 4.00 | 0.150 | 0.157 |
| e | 1.27 BSC | | 0.050 BSC | |
| L | 0.40 | 1.27 | 0.016 | 0.050 |

Embossed Carrier Tape & Reel Specification – SOIC Package



| | Millimetres | | Inches | |
|-------------|---------------|------|-----------------|-------|
| | Min | Max | Min | Max |
| E | 1.65 | 1.85 | 0.065 | 0.073 |
| F | 5.4 | 5.6 | 0.213 | 0.22 |
| P2 | 1.95 | 2.05 | 0.077 | 0.081 |
| D | 1.5 | 1.6 | 0.059 | 0.063 |
| D1 | 1.50 Min | | 0.059 Min | |
| P0 | 3.9 | 4.1 | 0.154 | 0.161 |
| 10P0 | 40.0 +/- 0.20 | | 1.574 +/- 0.008 | |
| W | 11.9 | 12.1 | 0.468 | 0.476 |
| P | 7.9 | 8.1 | 0.311 | 0.319 |
| A0 | 6.3 | 6.5 | 0.248 | 0.256 |
| B0 | 5.1 | 5.3 | 0.2 | 0.209 |
| K0 | 2 | 2.2 | 0.079 | 0.087 |
| t | 0.30 +/- 0.05 | | 0.012 +/- 0.002 | |