



# SC7538-08UTG

## 0.3pF Diode Array, Low Capacitance ESD Protection




**Note:** This package image is for example and reference only. For detail package drawing, please refer to the package section in this datasheet.

### Pinout




Top View



Bottom View

### Functional Block Diagram



### Description

The SC7538 integrates 8 channels of ultra low capacitance rail-to-rail diodes and an additional zener diode to provide protection for electronic equipment that may experience destructive electrostatic discharges (ESD). This robust device can safely absorb repetitive ESD strikes above the maximum level maximum level,  $\pm 8\text{kV}$  contact discharge, as specified in the international standard IEC 61000-4-2, without performance degradation standard ( $\pm 8\text{kV}$  contact discharge) without performance degradation. The extremely low loading capacitance also makes it ideal for protecting high speed signal pins such as V-By-One, HDMI, USB3.0, USB2.0, and IEEE 1394.

### Features & Benefits

- ESD, IEC 61000-4-2,  $\pm 22\text{kV}$  contact,  $\pm 30\text{kV}$  air
- EFT, IEC 61000-4-4, 40A ( $t_p=5/50\text{ns}$ )
- Surge Tolerance, IEC 61000-4-5 2nd edition, 3A ( $t_p=8/20\mu\text{s}$ )
- Low capacitance of 0.3pF @0V, 3GHz (TYP) per I/O
- Low leakage current of 0.5 $\mu\text{A}$  (MAX) at 5V
- Halogen free, Lead free and RoHS compliant

### Applications

- V-By-One
- Embedded DisplayPort
- USB 2.0/3.0 Ports
- HDMI
- Flat Panel Displays
- LCD/LED TVs
- Smartphones
- Mobile Computing

#### Life Support Note:

Not Intended for Use in Life Support or Life Saving Applications  
The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

# SC7538-08UTG

## 0.3pF Diode Array, Low Capacitance ESD Protection

### Absolute Maximum Ratings

| Symbol     | Parameter                        | Value      | Units |
|------------|----------------------------------|------------|-------|
| $I_{PP}$   | Peak Current ( $t_p=8/20\mu s$ ) | 3.0        | A     |
| $T_{OP}$   | Operating Temperature            | -40 to 125 | °C    |
| $T_{STOR}$ | Storage Temperature              | -55 to 150 | °C    |

**Caution:** Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the component at these or any other conditions above those indicated in the operational sections of this specification is not implied.


### Electrical Characteristics ( $T_{OP}=25^{\circ}C$ )

| Parameter                            | Symbol        | Test Conditions                     | Min      | Typ  | Max | Units    |
|--------------------------------------|---------------|-------------------------------------|----------|------|-----|----------|
| Reverse Standoff Voltage             | $V_{RWM}$     | Pin-1,-2,-4,-5,-6,-7,-8,-9 to pin-3 |          |      | 5   | V        |
| Breakdown Voltage                    | $V_{BR}$      | $I_R=1mA$                           | 6        |      |     | V        |
| Reverse Leakage Current              | $I_{LEAK}$    | $V_R=5V$ , I/O to GND               |          |      | 0.5 | $\mu A$  |
| Clamp Voltage <sup>1</sup>           | $V_C$         | $I_{PP}=1A$ , $t_p=8/20\mu s$ , Fwd |          | 9.9  |     | V        |
|                                      |               | $I_{PP}=2A$ , $t_p=8/20\mu s$ , Fwd |          | 10.9 |     |          |
| Dynamic Resistance <sup>2</sup>      | $R_{DYN}$     | TLP, $t_p=100ns$ , I/O to GND       |          | 0.42 |     | $\Omega$ |
| ESD Withstand Voltage <sup>1,3</sup> | $V_{ESD}$     | IEC 61000-4-2 (Contact Discharge)   | $\pm 22$ |      |     | kV       |
|                                      |               | IEC 61000-4-2 (Air Discharge)       | $\pm 30$ |      |     | kV       |
| Diode Capacitance <sup>1</sup>       | $C_{I/O-GND}$ | Reverse Bias=0V, $f=3GHz$           |          | 0.3  |     | pF       |


**Notes:**

- Parameter is guaranteed by design and/or component characterization.
- Transmission Line Pulse (TLP) test setting : Std.TDR(50 $\Omega$ ),  $t_p=100ns$ ,  $tr=0.2ns$  ITLP and VTLP averaging window: start  $t_1=70ns$  to end  $t_2=90ns$
- Device stressed with ten non-repetitive ESD pulses.

### 8/20 $\mu s$ Pulse Waveform






### Clamping Voltage vs IPP



**SC7538-08UTG**

0.3pF Diode Array, Low Capacitance ESD Protection


**Positive Transmission Line Pulsing (TLP) Plot****Negative Transmission Line Pulsing (TLP) Plot****IEC 61000-4-2 +8 kV Contact ESD Clamping Voltage****IEC 61000-4-2 -8 kV Contact ESD Clamping Voltage**

# SC7538-08UTG

## 0.3pF Diode Array, Low Capacitance ESD Protection

### Soldering Parameters

|  |                                    |                         |
|--|------------------------------------|-------------------------|
| <b>Reflow Condition</b>  |                                    | Pb – Free assembly      |
| <b>Pre Heat</b>  | - Temperature Min ( $T_{s(min)}$ ) | 150°C                   |
|  | - Temperature Max ( $T_{s(max)}$ ) | 200°C                   |
|  | - Time (min to max) ( $t_s$ )      | 60 – 120 secs           |
| <b>Average ramp up rate (Liquidus) Temp (<math>T_L</math>) to peak</b> |                                    | 3°C/second max          |
| <b><math>T_{s(max)}</math> to <math>T_L</math> - Ramp-up Rate</b>      |                                    | 3°C/second max          |
| <b>Reflow</b>  | - Temperature ( $T_L$ ) (Liquidus) | 217°C                   |
|  | - Temperature ( $t_L$ )            | 60 – 150 seconds        |
| <b>Peak Temperature (<math>T_p</math>)</b>                             |                                    | 260 <sup>+0/-5</sup> °C |
| <b>Time within 5°C of actual peak Temperature (<math>t_p</math>)</b>   |                                    | 30 seconds              |
| <b>Ramp-down Rate</b>  |                                    | 6°C/second max          |
| <b>Time 25°C to peak Temperature (<math>T_p</math>)</b>                |                                    | 8 minutes Max.          |
| <b>Do not exceed</b>   |                                    | 260°C                   |




### Ordering Information

| Part Number  | Package | Min. Order Qty. |
|--------------|---------|-----------------|
| SC7538-08UTG | μDFN-9  | 3000            |


### Product Characteristics

|                           |  |
|---------------------------|--|
| <b>Lead Plating</b>       | Matte Tin  |
| <b>Lead material</b>      | Copper Alloy   |
| <b>Substrate Material</b> | Silicon  |
| <b>Body Material</b>      | Molded Compound  |
| <b>Flammability</b>       | UL Recognized compound meeting flammability rating V-0 |

### Part Marking System




### Part Numbering System



# SC7538-08UTG



## 0.3pF Diode Array, Low Capacitance ESD Protection

### Package Dimensions





| Symbol    | μDFN-9 (3.8x1.0mm) |      |      | Inches    |       |       |
|-----------|--------------------|------|------|-----------|-------|-------|
|           | Min                | Nom  | Max  | Min       | Nom   | Max   |
| <b>A</b>  | 0.45               | 0.50 | 0.55 | 0.018     | 0.020 | 0.022 |
| <b>A1</b> | -                  | 0.02 | 0.05 | -         | 0.001 | 0.002 |
| <b>b</b>  | 0.15               | 0.20 | 0.25 | 0.006     | 0.008 | 0.010 |
| <b>c</b>  | 0.10               | 0.15 | 0.20 | 0.004     | 0.006 | 0.008 |
| <b>D</b>  | 3.70               | 3.80 | 3.90 | 0.146     | 0.150 | 0.154 |
| <b>e</b>  | 0.80 BSC           |      |      | 0.031 BSC |       |       |
| <b>e1</b> | 0.90 BSC           |      |      | 0.035 BSC |       |       |
| <b>E</b>  | 0.90               | 1.00 | 1.10 | 0.035     | 0.039 | 0.043 |
| <b>L</b>  | 0.20               | 0.30 | 0.40 | 0.008     | 0.012 | 0.016 |


### Embossed Carrier Tape & Reel Specification



| Symbol    | Millimeters         |
|-----------|---------------------|
| <b>A0</b> | 1.35 +/- 0.10       |
| <b>B0</b> | 4.00 +/- 0.05       |
| <b>D</b>  | Ø 1.50 + 0.1/- 0    |
| <b>D1</b> | Ø 1.00 +/- 0.05     |
| <b>E</b>  | 1.75 +/- 0.10       |
| <b>F</b>  | 5.50 +/- 0.05       |
| <b>K0</b> | 0.72 +/- 0.05       |
| <b>P</b>  | 4.00 +/- 0.10       |
| <b>P0</b> | 4.00 +/- 0.10       |
| <b>P2</b> | 2.00 +/- 0.05       |
| <b>T</b>  | 0.25 +/- 0.02       |
| <b>W</b>  | 12.00 + 0.30/- 0.10 |



8mm TAPE AND REEL



**Product Disclaimer:** Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. "Littelfuse" includes Littelfuse, Inc., and all of its affiliate entities. <http://www.littelfuse.com/disclaimer-electronics>

# SC7538-08UTG

## 0.3pF Diode Array, Low Capacitance ESD Protection

**Product Disclaimer:** Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. "Littelfuse" includes Littelfuse, Inc., and all of its affiliate entities. <http://www.littelfuse.com/disclaimer-electronics>.