IXYS


Preliminary Technical Information

# X2-Class Power MOSFET


# IXTA12N70X2
# IXTP12N70X2
# IXTH12N70X2

$V_{DSS}$ = 700V
$I_{D25}$ = 12A
$R_{DS(on)}$ ≤ 300mΩ


N-Channel Enhancement Mode





**TO-263 (IXTA)**




**TO-220 (IXTP)**




**TO-247 (IXTH)**




G = Gate D = Drain
S = Source Tab = Drain

| Symbol | Test Conditions | Maximum Ratings | |
|---|---|---|---|
| $V_{DSS}$ | $T_J$ = 25°C to 150°C | 700 | V |
| $V_{DGR}$ | $T_J$ = 25°C to 150°C, $R_{GS}$ = 1MΩ | 700 | V |
| $V_{GSS}$ | Continuous | ±30 | V |
| $V_{GSM}$ | Transient | ±40 | V |
| $I_{D25}$ | $T_C$ = 25°C | 12 | A |
| $I_{DM}$ | $T_C$ = 25°C, Pulse Width Limited by $T_{JM}$ | 24 | A |
| $I_A$ | $T_C$ = 25°C | 6 | A |
| $E_{AS}$ | $T_C$ = 25°C | 300 | mJ |
| dv/dt | $I_S \le I_{DM}$, $V_{DD} \le V_{DSS}$, $T_J \le 150°C$ | 50 | V/ns |
| $P_D$ | $T_C$ = 25°C | 180 | W |
| $T_J$ | | -55 ... +150 | °C |
| $T_{JM}$ | | 150 | °C |
| $T_{stg}$ | | -55 ... +150 | °C |
| $T_L$ | Maximum Lead Temperature for Soldering | 300 | °C |
| $T_{SOLD}$ | 1.6 mm (0.062in.) from Case for 10s | 260 | °C |
| $F_C$ | Mounting Force (TO-263) | 10..65 / 2.2..14.6 | N/lb |
| $M_d$ | Mounting Torque (TO-220 & TO-247) | 1.13 / 10 | Nm/lb.in |
| Weight | TO-263 | 2.5 | g |
| | TO-220 | 3.0 | g |
| | TO-247 | 6.0 | g |

| Symbol | Test Conditions ($T_J$ = 25°C, Unless Otherwise Specified) | Characteristic Values Min. | Typ. | Max. | |
|---|---|---|---|---|---|
| $BV_{DSS}$ | $V_{GS}$ = 0V, $I_D$ = 250μA | 700 | | | V |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$, $I_D$ = 250μA | 2.5 | | 4.5 | V |
| $I_{GSS}$ | $V_{GS}$ = ±30V, $V_{DS}$ = 0V | | | ±100 | nA |
| $I_{DSS}$ | $V_{DS} = V_{DSS}$, $V_{GS}$ = 0V | | | 5 | μA |
| | $T_J$ = 125°C | | | 75 | μA |
| $R_{DS(on)}$ | $V_{GS}$ = 10V, $I_D = 0.5 \bullet I_{D25}$, Note 1 | | | 300 | mΩ |

## Features

- International Standard Packages
- Low $R_{DS(ON)}$ and $Q_G$
- Avalanche Rated
- Low Package Inductance

## Advantages

- High Power Density
- Easy to Mount
- Space Savings

## Applications

- Switch-Mode and Resonant-Mode Power Supplies
- DC-DC Converters
- PFC Circuits
- AC and DC Motor Drives
- Robotics and Servo Controls

© 2018 IXYS CORPORATION, All Rights Reserved

| Symbol | Test Conditions ($T_J$ = 25°C, Unless Otherwise Specified) | Characteristic Values Min. | Typ. | Max | |
|---|---|---|---|---|---|
| $g_{fs}$ | $V_{DS}$ = 10V, $I_D$ = 0.5 • $I_{D25}$, Note 1 | 7 | 12 | | S |
| $R_{Gi}$ | Gate Input Resistance | | 3.7 | | Ω |
| $C_{iss}$ | $V_{GS}$ = 0V, $V_{DS}$ = 25V, f = 1MHz | | 960 | | pF |
| $C_{oss}$ | | | 920 | | pF |
| $C_{rss}$ | | | 2 | | pF |
| | **Effective Output Capacitance** | | | | |
| $C_{o(er)}$ | Energy related; $V_{GS}$ = 0V, $V_{DS}$ = 0.8 • $V_{DSS}$ | | 58 | | pF |
| $C_{o(tr)}$ | Time related; $V_{GS}$ = 0V, $V_{DS}$ = 0.8 • $V_{DSS}$ | | 200 | | pF |
| $t_{d(on)}$ | **Resistive Switching Times** | | 24 | | ns |
| $t_r$ | $V_{GS}$ = 10V, $V_{DS}$ = 0.5 • $V_{DSS}$, $I_D$ = 0.5 • $I_{D25}$ | | 30 | | ns |
| $t_{d(off)}$ | $R_G$ = 30Ω (External) | | 78 | | ns |
| $t_f$ | | | 27 | | ns |
| $Q_{g(on)}$ | $V_{GS}$ = 10V, $V_{DS}$ = 0.5 • $V_{DSS}$, $I_D$ = 0.5 • $I_{D25}$ | | 19 | | nC |
| $Q_{gs}$ | | | 5 | | nC |
| $Q_{gd}$ | | | 8 | | nC |
| $R_{thJC}$ | | | | 0.69 | °C/W |
| $R_{thCS}$ | TO-220 | | 0.50 | | °C/W |
| | TO-247 | | 0.25 | | °C/W |

**Source-Drain Diode**

| Symbol | Test Conditions ($T_J$ = 25°C, Unless Otherwise Specified) | Characteristic Values Min. | Typ. | Max | |
|---|---|---|---|---|---|
| $I_S$ | $V_{GS}$ = 0V | | | 12 | A |
| $I_{SM}$ | Repetitive, pulse Width Limited by $T_{JM}$ | | | 48 | A |
| $V_{SD}$ | $I_F$ = $I_S$, $V_{GS}$ = 0V, Note 1 | | | 1.4 | V |
| $t_{rr}$ | $I_F$ = 6A, -di/dt = 100A/μs | | 270 | | ns |
| $Q_{RM}$ | $V_R$ = 100V | | 2.8 | | μC |
| $I_{RM}$ | | | 21 | | A |

Note 1. Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.

**PRELIMINARY TECHNICAL INFORMATION**

The product presented herein is under development. The Technical Specifications offered are derived from a subjective evaluation of the design, based upon prior knowledge and experience, and constitute a "considered reflection" of the anticipated result. IXYS reserves the right to change limits, test conditions, and dimensions without notice.

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,860,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123B1 6,306,728B1 6,404,065B1 6,534,343 6,583,505 6,683,344 6,710,405B2 6,710,463 6,727,585 6,759,692 6,771,478B2 7,005,734B2 7,063,975B2 7,071,537 7,157,338B2

**Fig. 1. Output Characteristics @ $T_J$ = 25ºC**





**Fig. 2. Extended Output Characteristics @ $T_J$ = 25ºC**





**Fig. 3. Output Characteristics @ $T_J$ = 125ºC**





**Fig. 4. $R_{DS(on)}$ Normalized to $I_D$ = 6A Value vs. Junction Temperature**





**Fig. 5. $R_{DS(on)}$ Normalized to $I_D$ = 6A Value vs. Drain Current**






**Fig. 6. Normalized Breakdown & Threshold Voltages vs. Junction Temperature**




© 2018 IXYS CORPORATION, All Rights Reserved

**Fig. 7. Maximum Drain Current vs. Case Temperature**





**Fig. 8. Input Admittance**





**Fig. 9. Transconductance**





**Fig. 10. Forward Voltage Drop of Intrinsic Diode**





**Fig. 11. Gate Charge**






**Fig. 12. Capacitance**




IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

**Fig. 13. Output Capacitance Stored Energy**





**Fig. 14. Forward-Bias Safe Operating Area**







**Fig. 15. Maximum Transient Thermal Impedance**




© 2018 IXYS CORPORATION, All Rights Reserved


## TO-263 Outline




1 - Gate
2,4 - Drain
3 - Source

| SYM | INCHES | | MILLIMETER | |
|---|---|---|---|---|
| | MIN | MAX | MIN | MAX |
| A | .170 | .185 | 4.30 | 4.70 |
| A1 | .000 | .008 | 0.00 | 0.20 |
| A2 | .091 | .098 | 2.30 | 2.50 |
| b | .028 | .035 | 0.70 | 0.90 |
| b2 | .046 | .060 | 1.18 | 1.52 |
| C | .018 | .024 | 0.45 | 0.60 |
| C2 | .049 | .060 | 1.25 | 1.52 |
| D | .340 | .370 | 8.63 | 9.40 |
| D1 | .300 | .327 | 7.62 | 8.30 |
| E | .380 | .410 | 9.65 | 10.41 |
| E1 | .270 | .330 | 6.86 | 8.38 |
| e | .100 BSC | | 2.54 BSC | |
| H | .580 | .620 | 14.73 | 15.75 |
| L | .075 | .105 | 1.91 | 2.67 |
| L1 | .039 | .060 | 1.00 | 1.52 |
| L2 | — | .070 | — | 1.77 |
| L3 | .010 BSC | | 0.254 BSC | |


## TO-220 Outline




1 - Gate
2,4 - Drain
3 - Source

| SYM | INCHES | | MILLIMETERS | |
|---|---|---|---|---|
| | MIN | MAX | MIN | MAX |
| A | .169 | .185 | 4.30 | 4.70 |
| A1 | .047 | .055 | 1.20 | 1.40 |
| A2 | .079 | .106 | 2.00 | 2.70 |
| b | .024 | .039 | 0.60 | 1.00 |
| b2 | .045 | .057 | 1.15 | 1.45 |
| c | .014 | .026 | 0.35 | 0.65 |
| D | .587 | .626 | 14.90 | 15.90 |
| D1 | .335 | .370 | 8.50 | 9.40 |
| (D2) | .500 | .531 | 12.70 | 13.50 |
| E | .382 | .406 | 9.70 | 10.30 |
| (E1) | .283 | .323 | 7.20 | 8.20 |
| e | .100 BSC | | 2.54 BSC | |
| e1 | .200 BSC | | 5.08 BSC | |
| H1 | .244 | .268 | 6.20 | 6.80 |
| L | .492 | .547 | 12.50 | 13.90 |
| L1 | .110 | .154 | 2.80 | 3.90 |
| ØP | .134 | .150 | 3.40 | 3.80 |
| Q | .106 | .126 | 2.70 | 3.20 |

## TO-247 Outline




1 - Gate
2,4 - Drain
3 - Source

| SYM | INCHES | | MILLIMETERS | |
|---|---|---|---|---|
| | MIN | MAX | MIN | MAX |
| A | .190 | .205 | 4.83 | 5.21 |
| A1 | .090 | .100 | 2.29 | 2.54 |
| A2 | .075 | .085 | 1.91 | 2.16 |
| b | .045 | .055 | 1.14 | 1.40 |
| b2 | .075 | .087 | 1.91 | 2.20 |
| b4 | .115 | .126 | 2.92 | 3.20 |
| C | .024 | .031 | 0.61 | 0.80 |
| D | .819 | .840 | 20.80 | 21.34 |
| D1 | .650 | .690 | 16.51 | 17.53 |
| D2 | .035 | .050 | 0.89 | 1.27 |
| E | .620 | .635 | 15.75 | 16.13 |
| E1 | .545 | .565 | 13.84 | 14.35 |
| e | .215 BSC | | 5.45 BSC | |
| J | -- | .010 | -- | 0.25 |
| K | -- | .025 | -- | 0.64 |
| L | .780 | .810 | 19.81 | 20.57 |
| L1 | .150 | .170 | 3.81 | 4.32 |
| øP | .140 | .144 | 3.55 | 3.65 |
| øP1 | .275 | .290 | 6.99 | 7.37 |
| Q | .220 | .244 | 5.59 | 6.20 |
| R | .170 | .190 | 4.32 | 4.83 |
| S | .242 BSC | | 6.15 BSC | |

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.




Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.