


Breakover Diode Modules (BOD1)

$$V_{BO} = 1200 - 4200 \text{ V}$$

$$I_{AVM} = 0.2 - 1.25 \text{ A}$$

Number of BODs	Types
2	IXBOD1-12R(D) ... IXBOD1-19R(D)
3	IXBOD1-20R(D) ... IXBOD1-32R(D)
4	IXBOD1-34R ... IXBOD1-42R



Features / Advantages:

- Fast turn on
- Low temperature dependence
- Low leakage current

Applications:

- High voltage circuit protection
- Transient voltage protection
- Trigger device
- Power pulse generators
- Lightning and arcing protection
- Energy discharge circuits
- Battery overvoltage protection
- Solar array protection

Package: BOD-Package

- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0
- Soldering pins for PCB mounting
- Reduced weight

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

IXBOD1 several values				Ratings			
Symbol	Definitions	Conditions		min.	typ.	max.	
I_D	drain current	$V_D = 0.8 \cdot V_{BO}$	$T_{VJ} = 125^\circ\text{C}$			100	μA
I_{BO}	breakover current		$T_{VJ} = 25^\circ\text{C}$			15	mA
I_H	holding current		$T_{VJ} = 25^\circ\text{C}$			30	mA
V_H	holding voltage		$T_{VJ} = 25^\circ\text{C}$	4		8	V
$(di/dt)_C$	maximum pulsed source current	$V_D = V_{BO}; I_T = 80 \text{ A}; f = 50 \text{ Hz}$	$T_{VJ} = 125^\circ\text{C}$			200	A/ μs
t_q	turn-off time	$V_D = 0.67 \cdot V_{BO}; V_R = 0 \text{ V}; I_T = 80 \text{ A}$ $dv/dt_{(lin.)} = 200 \text{ V}/\mu\text{s}; di/dt = -10 \text{ A}/\mu\text{s}$	$T_{VJ} = 125^\circ\text{C}$		150		μs
K_T	temperature coefficient of V_{BO}					$2 \cdot 10^{-3}$	K^{-1}
K_P	coefficient for energy per pulse E_P	(material constant)				700	K/Ws

IXBOD1 - 12R... - 19R (2 Elements)				Ratings			
Symbol	Definitions	Conditions		min.	typ.	max.	
V_{BO}	breakover voltage	$V_{BO}(T_{VJ}) = V_{BO, 25^\circ\text{C}} [1 + K_T (T_{VJ} - 25^\circ\text{C})]$					
		IXBOD 1 -12R		1150	1200	1250	V
		IXBOD 1 -13R		1250	1300	1350	V
		IXBOD 1 -14R		1350	1400	1450	V
		IXBOD 1 -15R		1450	1500	1550	V
		IXBOD 1 -16R		1550	1600	1650	V
		IXBOD 1 -17R		1650	1700	1750	V
		IXBOD 1 -18R		1750	1800	1850	V
		IXBOD 1 -19R		1850	1900	1950	V
I_{RMS}	RMS current	$f = 50 \text{ Hz}$ pins soldered to printed circuit (conductor 0.035x2mm)	$T_{amb} = 50^\circ\text{C}$			2.0	A
I_{FAVM}	maximum average forward current					1.25	A
I_{SM}	maximum pulsed source current	$t_p = 0.1 \text{ ms}; \text{non repetitive}$	$T_{amb} = 50^\circ\text{C}$			200	A
I^2t	I^2t value for fusing	$t_p = 0.1 \text{ ms}$	$T_{amb} = 50^\circ\text{C}$			2	A^2s
V_T	forward voltage drop	$I_T = 5 \text{ A}$	$T_{VJ} = 125^\circ\text{C}$			3.4	V
V_{T0}	threshold voltage	for power-loss calculation only				2.2	V
r_T	slope resistance					0.24	Ω

IXBOD1 - 12RD... - 19RD (2 Elements)				Ratings			
Symbol	Definitions	Conditions	min.	typ.	max.		
V_{BO}	<i>breakover voltage</i>	$V_{BO} (T_{VJ}) = V_{BO, 25^{\circ}C} [1 + K_T (T_{VJ} - 25^{\circ}C)]$					
		IXBOD 1 -12RD	1150	1200	1250		V
		IXBOD 1 -13RD	1250	1300	1350		V
		IXBOD 1 -14RD	1350	1400	1450		V
		IXBOD 1 -15RD	1450	1500	1550		V
		IXBOD 1 -16RD	1550	1600	1650		V
		IXBOD 1 -17RD	1650	1700	1750		V
		IXBOD 1 -18RD	1750	1800	1850		V
		IXBOD 1 -19RD	1850	1900	1950		V
I_{RMS}	<i>RMS current</i>	$f = 50 \text{ Hz}$ pins soldered to printed circuit (conductor 0.035x2mm) $T_{amb} = 50^{\circ}C$			0.3		A
I_{FAVM}	<i>maximum average forward current</i>				0.2		A
I_{SM}	<i>maximum pulsed source current</i>	$t_p = 0.1 \text{ ms}$; non repetitive $T_{amb} = 50^{\circ}C$			50		A
I^2t	<i>I²t value for fusing</i>	$t_p = 0.1 \text{ ms}$ $T_{amb} = 50^{\circ}C$			0.125		A ² s
V_T	<i>forward voltage drop</i>	$I_T = 5 \text{ A}$ $T_{VJ} = 125^{\circ}C$			27		V
V_{TO}	<i>threshold voltage</i>	for power-loss calculation only			17.5		V
r_T	<i>slope resistance</i>				3		Ω

IXBOD1 - 20R... - 32R (3 Elements)				Ratings			
Symbol	Definitions	Conditions	min.	typ.	max.		
V_{BO}	<i>breakover voltage</i>	$V_{BO} (T_{VJ}) = V_{BO, 25^{\circ}C} [1 + K_T (T_{VJ} - 25^{\circ}C)]$					
		IXBOD 1 -20R	1950	2000	2050		V
		IXBOD 1 -21R	2050	2100	2150		V
		IXBOD 1 -22R	2150	2200	2250		V
		IXBOD 1 -23R	2250	2300	2350		V
		IXBOD 1 -24R	2350	2400	2450		V
		IXBOD 1 -25R	2450	2500	2550		V
		IXBOD 1 -26R	2500	2600	2700		V
		IXBOD 1 -28R	2700	2800	2900		V
		IXBOD 1 -30R	2900	3000	3100		V
		IXBOD 1 -32R	3100	3200	3300		V
I_{RMS}	<i>RMS current</i>	$f = 50 \text{ Hz}$ pins soldered to printed circuit (conductor 0.035x2mm) $T_{amb} = 50^{\circ}C$			1.4		A
I_{FAVM}	<i>maximum average forward current</i>				0.9		A
I_{SM}	<i>maximum pulsed source current</i>	$t_p = 0.1 \text{ ms}$; non repetitive $T_{amb} = 50^{\circ}C$			200		A
I^2t	<i>I²t value for fusing</i>	$t_p = 0.1 \text{ ms}$ $T_{amb} = 50^{\circ}C$			2		A ² s
V_T	<i>forward voltage drop</i>	$I_T = 5 \text{ A}$ $T_{VJ} = 125^{\circ}C$			5.1		V
V_{TO}	<i>threshold voltage</i>	for power-loss calculation only			3.3		V
r_T	<i>slope resistance</i>				0.36		Ω


IXBOD1 - 20RD... - 32RD (3 Elements)			Ratings			
Symbol	Definitions	Conditions	min.	typ.	max.	
V_{BO}	<i>breakover voltage</i>	$V_{BO} (T_{VJ}) = V_{BO, 25^{\circ}C} [1 + K_T (T_{VJ} - 25^{\circ}C)]$				
		IXBOD 1 -20RD	1950	2000	2050	V
		IXBOD 1 -21RD	2050	2100	2150	V
		IXBOD 1 -22RD	2150	2200	2250	V
		IXBOD 1 -23RD	2250	2300	2350	V
		IXBOD 1 -24RD	2350	2400	2450	V
		IXBOD 1 -25RD	2450	2500	2550	V
		IXBOD 1 -26RD	2500	2600	2700	V
		IXBOD 1 -28RD	2700	2800	2900	V
		IXBOD 1 -30RD	2900	3000	3100	V
		IXBOD 1 -32RD	3100	3200	3300	V
I_{RMS}	<i>RMS current</i>	$f = 50 \text{ Hz}$ pins soldered to printed circuit (conductor 0.035x2mm) $T_{amb} = 50^{\circ}C$			0.3	A
I_{FAVM}	<i>maximum average forward current</i>				0.2	A
I_{SM}	<i>maximum pulsed source current</i>	$t_p = 0.1 \text{ ms}$; non repetitive $T_{amb} = 50^{\circ}C$			50	A
I^2t	<i>I²t value for fusing</i>	$t_p = 0.1 \text{ ms}$ $T_{amb} = 50^{\circ}C$			0.125	A ² s
V_T	<i>forward voltage drop</i>	$I_T = 5 \text{ A}$ $T_{VJ} = 125^{\circ}C$			27	V
V_{T0}	<i>threshold voltage</i>	for power-loss calculation only			17.5	V
r_T	<i>slope resistance</i>				3	Ω

IXBOD1 - 34... - 42R (4 Elements)			Ratings			
Symbol	Definitions	Conditions	min.	typ.	max.	
V_{BO}	<i>breakover voltage</i>	$V_{BO} (T_{VJ}) = V_{BO, 25^{\circ}C} [1 + K_T (T_{VJ} - 25^{\circ}C)]$				
		IXBOD 1 -34R	3300	3400	3500	V
		IXBOD 1 -36R	3500	3600	3700	V
		IXBOD 1 -38R	3700	3800	4000	V
		IXBOD 1 -40R	3900	4000	4100	V
		IXBOD 1 -42R	4100	4200	4300	V
I_{RMS}	<i>RMS current</i>	$f = 50 \text{ Hz}$ pins soldered to printed circuit (conductor 0.035x2mm) $T_{amb} = 50^{\circ}C$			1.1	A
I_{FAVM}	<i>maximum average forward current</i>				0.7	A
I_{SM}	<i>maximum pulsed source current</i>	$t_p = 0.1 \text{ ms}$; non repetitive $T_{amb} = 50^{\circ}C$			200	A
I^2t	<i>I²t value for fusing</i>	$t_p = 0.1 \text{ ms}$ $T_{amb} = 50^{\circ}C$			2	A ² s
V_T	<i>forward voltage drop</i>	$I_T = 5 \text{ A}$ $T_{VJ} = 125^{\circ}C$			6.8	V
V_{T0}	<i>threshold voltage</i>	for power-loss calculation only			4.4	V
r_T	<i>slope resistance</i>				0.48	Ω

Package FP-Case				Ratings			
Symbol	Definitions	Conditions	min.	typ.	max.		
T_{amb}	ambient temperature (cooling medium)		-40		125	°C	
T_{stg}	storage temperature		-40		125	°C	
T_{VJM}	maximum virtual junction temperature		-40		125	°C	
R_{thJA}	thermal resistance junction to ambient	natural convection with air speed 2 m/s			20 16	K/W K/W	
Weight				14			g



Outlines FP-case





Ordering	Part Name	Marking on Product	Delivering Mode	Base Qty	Ordering Code
Standard	IXBOD 1 -12R	IXBOD 1 -12R	Box	20	468649
Standard	IXBOD 1 -12RD	IXBOD 1 -12RD	Box	20	472948
Standard	IXBOD 1 -13R	IXBOD 1 -13R	Box	20	468657
Standard	IXBOD 1 -13RD	IXBOD 1 -13RD	Box	20	472956
Standard	IXBOD 1 -14R	IXBOD 1 -14R	Box	20	468665
Standard	IXBOD 1 -14RD	IXBOD 1 -14RD	Box	20	472964
Standard	IXBOD 1 -15R	IXBOD 1 -15R	Box	20	468673
Standard	IXBOD 1 -15RD	IXBOD 1 -15RD	Box	20	472972
Standard	IXBOD 1 -16R	IXBOD 1 -16R	Box	20	468681
Standard	IXBOD 1 -16RD	IXBOD 1 -16RD	Box	20	472794
Standard	IXBOD 1 -17R	IXBOD 1 -17R	Box	20	468703
Standard	IXBOD 1 -17RD	IXBOD 1 -17RD	Box	20	472980
Standard	IXBOD 1 -18R	IXBOD 1 -18R	Box	20	468711
Standard	IXBOD 1 -18RD	IXBOD 1 -18RD	Box	20	472999
Standard	IXBOD 1 -19R	IXBOD 1 -19R	Box	20	468738
Standard	IXBOD 1 -19RD	IXBOD 1 -19RD	Box	20	473006
Standard	IXBOD 1 -20R	IXBOD 1 -20R	Box	20	468746
Standard	IXBOD 1 -20RD	IXBOD 1 -20RD	Box	20	473014
Standard	IXBOD 1 -21R	IXBOD 1 -21R	Box	20	468754
Standard	IXBOD 1 -21RD	IXBOD 1 -21RD	Box	20	473022
Standard	IXBOD 1 -22R	IXBOD 1 -22R	Box	20	468762
Standard	IXBOD 1 -22RD	IXBOD 1 -22RD	Box	20	473030
Standard	IXBOD 1 -23R	IXBOD 1 -23R	Box	20	468770
Standard	IXBOD 1 -23RD	IXBOD 1 -23RD	Box	20	472786
Standard	IXBOD 1 -24R	IXBOD 1 -24R	Box	20	468789
Standard	IXBOD 1 -24RD	IXBOD 1 -24RD	Box	20	473049
Standard	IXBOD 1 -25R	IXBOD 1 -25R	Box	20	468797
Standard	IXBOD 1 -25RD	IXBOD 1 -25RD	Box	20	473057
Standard	IXBOD 1 -26R	IXBOD 1 -26R	Box	20	468800
Standard	IXBOD 1 -26RD	IXBOD 1 -26RD	Box	20	473065
Standard	IXBOD 1 -28R	IXBOD 1 -28R	Box	20	468819
Standard	IXBOD 1 -28RD	IXBOD 1 -28RD	Box	20	473073
Standard	IXBOD 1 -30R	IXBOD 1 -30R	Box	20	468827
Standard	IXBOD 1 -30RD	IXBOD 1 -30RD	Box	20	473081
Standard	IXBOD 1 -32R	IXBOD 1 -32R	Box	20	468835
Standard	IXBOD 1 -32RD	IXBOD 1 -32RD	Box	20	473103
Standard	IXBOD 1 -34R	IXBOD 1 -34R	Box	20	468843
Standard	IXBOD 1 -36R	IXBOD 1 -36R	Box	20	468851
Standard	IXBOD 1 -38R	IXBOD 1 -38R	Box	20	468878
Standard	IXBOD 1 -40R	IXBOD 1 -40R	Box	20	468886
Standard	IXBOD 1 -42R	IXBOD 1 -42R	Box	20	468894



Curves




Fig. 1 Energy per pulse for single BOD element for trapezoidal wave current. E_p must be multiplied by number of elements for total energy




Fig. 2 Energy per pulse for single BOD element for exponentially decaying current pulse. E_p must be multiplied by number of elements for total energy




Fig. 3 On-state voltage at $T_{vj} = 125^\circ\text{C}$




Fig. 4 Transient thermal resistance