

RESISTANCE @ +25°C = 10,000 ± 10%
RESISTANCE/TEMPERATURE CURVE = "E1"
BETA "β" (+25 TO +85°C) = 3,435°K NOMINAL
TEMPERATURE COEFFICIENT @ +25°C = −3.82%/°C NOMINAL
DISSIPATION CONSTANT = 0.7 mW/°C NOMINAL (AIR)
THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (AIR)
MAXIMUM TEMPERATURE RATING = +300°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

REV	REVISION RECORD	DATE	APP
NONE	RELEASE TO PRODUCTION	03/18/14	DD

SCALE NONE	U.S. SENSOR CORP.
DRAWN BY DAN DANKERT	© COPYRIGHT
DATE 03/18/14	714-639-1000 www.ussensor.com
REV. NONE	NTC THERMISTOR
LAYER 0 OF 2	P/N GS103E1K