




RESISTANCE @ +25°C = 20,000 Ω ± 1%  
 RESISTANCE/TEMPERATURE CURVE = "N1"  
 BETA "β" (+25 TO +50°C) = 4,050°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C = -4.50%/°C NOMINAL  
 MAXIMUM TEMPERATURE RATING = +125°C

|     |                 |          |     |
|-----|-----------------|----------|-----|
|     |                 |          |     |
| --- | ISO RELEASE     | 09/20/10 | DD  |
| REV | REVISION RECORD | DATE     | APP |

|          |             |                               |  |
|----------|-------------|-------------------------------|--|
| SCALE    | NONE        | © COPYRIGHT                   |  |
| DRAWN BY | DAN DANKERT | U.S. SENSOR CORP.             |  |
| DATE     | 09/20/10    | 714-639-1000 www.ussensor.com |  |
| REV.     | NONE        | NTC THERMISTOR                |  |
| LAYER    | 0 OF 1      | P/N KC203N3F                  |  |