




RESISTANCE @ +25°C = 1,000 Ω $\pm$ 10%
 RESISTANCE/TEMPERATURE CURVE = "F"
 TEMPERATURE COEFFICIENT @ +25°C = -3.86%/°C NOMINAL
 BETA " β " (0 TO +50°C) = 3,419°K NOMINAL
 DISSIPATION CONSTANT = 3 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 15 SECONDS MAXIMUM (STILL AIR)
 THERMAL TIME CONSTANT = 2 SECONDS MAXIMUM (WELL STIRRED OIL)
 MAXIMUM TEMPERATURE RATING = +150°C

REV	REVISION RECORD	DATE	APP
"A"	MAXIMUM DIAMETER WAS 0.125"	10/01/97	TW
---	ISO RELEASE	07/09/03	DD
"B"	MAXIMUM DIAMETER WAS 0.140"	11/03/11	DD

SCALE NONE	© COPYRIGHT U.S. SENSOR CORP. 714-639-1000 www.ussensor.com NTC THERMISTOR P/N DC102F2K
DRAWN BY DAN DANKERT	
DATE 05/23/96	
REV. "B"	
LAYER 0 OF 1	